



LL500Z | Maxos fusion Acc., White

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

General Information

Service Tag	Yes
Value ladder	Specification


Operating and Electrical

Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-

Mechanical and Housing

Overall length	2,275 mm
Overall width	60 mm
Overall height	8.5 mm
Dimensions (height x width x depth)	9 x 60 x 2275 mm
Material	Polycarbonate
Ingress protection code	-
Mech. impact protection code	IK00 [No protection]
Accessory colour	White
Net Weight (Piece)	0.180 kg

Dimensional drawing



Related Documents

Documents and certificates	Document Name	Download
Tender text	Tender_Text_910925864236_en_GB.txt	Download 

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Product Data

Order product name	LL500Z BC L2300 WH
Full product name	LL500Z BC L2300 WH
Full EOC	871869638354499
Order code	910925864236
Material no. (12 NC)	910925864236
Numerator – quantity per pack	1
EAN/UPC — Product/Case	8718696383544
Numerator – packs per outer box	20
EAN/UPC - Case	8720169965096
Product family code	LL500Z [Maxos fusion Acc.]