



Maxos fusion

LL512Z CD WH

LL512Z | Maxos fusion Acc., White

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Product data

General Information	
Service tag	Yes
Value ladder	Specification
Warranty period	5 years
Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-
Mechanical and Housing	
Housing Material	Steel
Fixation material	Stainless steel
Housing Color	White

Overall length	1,137 mm
Overall width	63 mm
Overall height	42 mm
Dimensions (Height x Width x Depth)	42 x 63 x 1137 mm
Material	Steel
Ingress protection code	-
Mech. impact protection code	IK02 [0.2 J standard]
Accessory color	White
Net Weight (Piece)	0.930 kg

Approval and Application	
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes

Maxos fusion

EU RoHS compliant	Yes
Product Data	
Order product name	LL512Z CD WH
Full product name	LL512Z CD WH
Full product code	871869637464199
Order code	910925864240
Material Nr. (12NC)	910925864240

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696374641
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696383582
Product family code	LL512Z [Maxos fusion Acc.]

Dimensional drawing

