



Maxos fusion

LL512Z CD SI

LL512Z | Maxos fusion Acc., Silver

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Product data

General Information			
Service Tag	Yes	Overall length	1,137 mm
Value ladder	Specification	Overall width	63 mm
Warranty period	5 years	Overall height	42 mm
		Dimensions (height x width x depth)	42 x 63 x 1137 mm
		Material	Steel
		Ingress protection code	-
		Mech. impact protection code	IK02 [0.2 J standard]
		Accessory colour	Silver
		Net Weight (Piece)	0.930 kg
Operating and Electrical		Approval and Application	
Input Voltage	- V	Flammability mark	For mounting on normally flammable surfaces
Line Frequency	- Hz	CE mark	Yes
Protection class IEC	-		
Mechanical and Housing			
Housing material	Steel		
Fixation material	Stainless steel		
Housing Colour	Silver		

Maxos fusion

EU RoHS compliant	Yes
Product Data	
Order product name	LL512Z CD SI
Full product name	LL512Z CD SI
Full EOC	871869637465899
Order code	910925864241
Material no. (12 NC)	910925864241

Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696374658
Numerator – packs per outer box	10
EAN/UPC - Case	8718696383599
Product family code	LL512Z [Maxos fusion Acc.]

Dimensional drawing

