



Maxos fusion

LL546Z CD WH

LL546Z | Maxos fusion Acc., White

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Product data

General Information		Overall length	
Service Tag	Yes	Overall width	4,551 mm
Value ladder	Specification	Overall height	63 mm
Warranty period	5 years	Dimensions (height x width x depth)	42 mm
Operating and Electrical		Material	42 x 63 x 4551 mm
Input Voltage	- V	Ingress protection code	Steel
Line Frequency	- Hz	Mech. impact protection code	-
Protection class IEC	-	Accessory colour	IK02 [0.2 J standard]
Mechanical and Housing		Net Weight (Piece)	White
Housing material	Steel	Approval and Application	3.780 kg
Fixation material	Stainless steel	Flammability mark	For mounting on normally flammable surfaces
Housing Colour	White	CE mark	Yes

Maxos fusion

EU RoHS compliant	Yes
Product Data	
Order product name	LL546Z CD WH
Full product name	LL546Z CD WH
Full EOC	871869637470299
Order code	910925864246
Material no. (12 NC)	910925864246

Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696374702
Numerator – packs per outer box	10
EAN/UPC - Case	8718696383643
Product family code	LL546Z [Maxos fusion Acc.]

Dimensional drawing

