



## Mini 300 LED gen3, Under-canopy light, 48 W, 7462 lm, 4000 K, CRI70, Internal (no external connection), Petrol rotational symmetric medium, IP66

Mini 300 LED gen3 luminaires, perfect product design and latest LED technology combination for highly efficient light outputs can turn your petrol station into a branded landmark and help visitors to approach safely in visual comfort. Mini 300 LED gen3, the state-of-the-art LED luminaires with light on-demand intelligent motion-sensing control system takes energy saving to new levels with dimming, but at the same time, ensuring sufficient lighting for orientation and safety. The lighting scenarios can be customised to your preference during the initial installation or during the product's lifespan. The optional Master-Slave combination with a built-in presence and light sensor there's no need for an external sensor and one Master Mini 300 LED

gen3 can control up to 6 basic luminaires. This will not only positively impact your investment but can also lead to additional energy savings. The Mini 300 LED Gen3 luminaire is so lightweight that it can be effortlessly installed by one person. Luminaire settings can even be changed from ground level using a smartphone or tablet as a remote-control, eliminating the need to work at height. With the free Mini 300 LED App, even the status of the luminaire can be read while standing on the floor. The Mini 300 LED gen3 luminaires in recessed mounted, surface-mounted and floodlight versions, which are suitable for undercanopy lighting, is a breakthrough, retrofit solution reduces installation costs.

## General Information

Lamp family code	LED81 [LED module 8100 lm]
Light source replaceable	Yes
Number of gear units	Unit
Driver included	Yes
Light source engine type	LED
Service Tag	Yes
Lighting Technology	LED
Value ladder	Specification
Warranty period	5 years

## Light Technical

Upwards light output ratio	0
Luminous Flux	7,462 lm
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	155 lm/W
Colour rendering index (CRI)	70
Light source colour	740 neutral white
Luminaire light beam spread	113°
Optic type outdoor	Petrol rotational symmetric medium
Effective projected area	0.0314 m <sup>2</sup>

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	48 W
Power Factor (Fraction)	0.98
Connection	Screw connector
Cable	-
Number of products on MCB (16 A type B)	11
Protection class IEC	Safety class I
Surge Protection (Common/Differential)	Standard surge protection level
Total harmonic distortion	11 %

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	Internal (no external connection)
Constant light output	No
Maximum dim level	10%

## Mechanical and Housing

Housing material	Aluminium die cast
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Polycarbonate
Fixation material	Aluminium
Housing Colour	White
Mounting device	-
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	346 mm
Overall width	346 mm
Overall height	139 mm
Dimensions (height x width x depth)	139 x 346 x 346 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Standard tilt angle post-top	-
Standard tilt angle side entry	-
Optical cover type	Polycarbonate bowl/cover flat
Net Weight (Piece)	6.050 kg

## Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating the performance of LED -based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Ambient temperature range	-40 to +50 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Colour Rendering Index Tolerance	+/-2
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 35,000 h	35 %
Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 50,000 h	75 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 35000 h	L99
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L98
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 75000 h	L97
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L97

## Sustainability Data

Sustainability rating	Signify Circle
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.


## Product Data

Order product name	BCP333 LED81/740 I PRM
Full product name	BCP333 LED81/740 I PRM
Full EOC	871869699766600
Order code	910925865288

Material no. (12 NC)	910925865288
Local order code	BCP333
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696997666

Numerator – packs per outer box	1
EAN/UPC – Case	8718696997666
Product family code	BCP333 [MINI 300 LED GEN3]

**Dimensional drawing**



**Polar normal diagrams**

