



# Mini 300 LED gen3

## BBP333 LED128/757 I PAM D9 SNS

Mini 300 LED gen3, Under-canopy light, 74 W, 10920 lm, 5700 K, CRI70, Internal (no external connection), Petrol asymmetric medium, IP66

Mini 300 LED gen3 luminaires, perfect product design and latest LED technology combination for highly efficient light outputs can turn your petrol station into a branded landmark and help visitors to approach safely in visual comfort. Mini 300 LED gen3, the state-of-the-art LED luminaires with light on demand intelligent motion sensing control system takes energy saving to new levels with dimming, but at the same time, ensuring sufficient lighting for orientation and safety. The light scenarios can be tailored to your preference at the first installation or during the lifespan of the products. The optional Master-Slave combination with a built-in presence and light sensor there's no need for an external sensor and one Master Mini 300 LED gen3 can control up to 6 basic luminaires. Not only will this have a positive impact on your investment, it can also lead to additional energy saving. Mini 300 LED gen3 luminaire is so light that it can be installed effortlessly by one person. Luminaire settings can even be changed from ground level using a smart phone or tablet as a remote control, eliminating the need to work at height. With the free Mini 300 LED App, even the status of the luminaire can be read while standing on the floor. The Mini 300 LED gen3 luminaires in recessed mounted, surface mounted and floodlight versions, which are suitable for undercanopy lighting, is a breakthrough, retrofit solution reduces installation costs.

### Product data

General Information		Lighting Technology	
Lamp family code	LED128 [LED module 12800 lm]	Driver included	Yes
Light source replaceable	Yes	Light source engine type	LED
Number of gear units	1 unit	Service tag	Yes
		Lighting Technology	LED

## Mini 300 LED gen3

Value ladder	Specification
Warranty period	5 years

### Light Technical

Upward light output ratio	0
Luminous Flux	10,920 lm
Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	148 lm/W
Color rendering index (CRI)	70
Light source color	757 cool white
Luminaire light beam spread	113°
Optic type outdoor	Petrol asymmetric medium
Effective projected area	0.0584 m <sup>2</sup>

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	74 W
Power Factor (Fraction)	0.99
Connection	Push-in connector 5-pole
Cable	Cable without plug 3-pole
Number of products on MCB of 16 A type B	8
Protection class IEC	Safety class I
Surge Protection (Common/Differential)	Standard surge protection level
Total harmonic distortion	8.4 %

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	Internal (no external connection)
Constant light output	No
DALI Standard	DALI-2™
Maximum dim level	10%

### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Acrylate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Mounting device	-
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	335 mm
Overall width	335 mm
Overall height	92 mm
Dimensions (Height x Width x Depth)	92 x 335 x 335 mm

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Optical cover type	Polycarbonate bowl/cover flat
Net Weight (Piece)	3.880 kg

### Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Ambient temperature range	-40 to +50 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.341, 0.329) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 35000 h	35 %
Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 75000 h	75 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 35000 h	L99
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L98
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 75000 h	L97
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L96

### Sustainability Data


Sustainability rating	Signify Circle
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and

## Mini 300 LED gen3


	documentation are available for an extended period of time.
<b>Embedded carbon (A1-A3)</b>	74.5 kg CO <sub>2e</sub>
<b>Product non-virgin material ratio</b>	16.6 %
<b>Recyclable content ratio of the finished product</b>	42.2 %
<b>GWP total B6 (kg CO<sub>2</sub>eq) Declared Unit</b>	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO <sub>2</sub> eq / kWh)
<b>GWP total B6 (kg CO<sub>2</sub>eq) Functional Unit</b>	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared

	Unit * 35000 (hrs) * Energy mix (kg CO <sub>2</sub> eq / kWh)
<b>Product Data</b>	
<b>Order product name</b>	BBP333 LED128/757 I PAM D9 SNS
<b>Full product name</b>	BBP333 LED128/757 I PAM D9 SNS
<b>Full product code</b>	871869981944600
<b>Order code</b>	910925866262
<b>Material Nr. (12NC)</b>	910925866262
<b>Numerator - Quantity Per Pack</b>	1
<b>EAN/UPC - Product/Case</b>	8718699819446
<b>Numerator - Packs per outer box</b>	1
<b>EAN/UPC - Case</b>	8718699819446
<b>Product family code</b>	BBP333 [Mini 300 LED gen3]

### Dimensional drawing



### Photometric data



Polar Normal (separate) - BBP333I - 910925866262

## Mini 300 LED gen3

