



FlexBlend, Suspended

SP342P 45S/940 DEIA MLO SMT L150 SI

FlexBlend, Suspended, 42.5 W, 1470x200 mm; H73 mm, SMT, 4500 lm, 4000 K, CRI>90, DALI, UGR19

Philips FlexBlend is an attractive family of surface mounted and suspended luminaires, next to Flexblend recessed. The luminaire range is enabling building owners to advance their lighting operations, by offering office-compliant lighting with a return on investment of less than 3 to 4 years. FlexBlend provides the required flexibility through the adaptability in design. This gives the possibility to install the luminaires easily in the field, at any moment. Even when today's luminaire is suspended, tomorrow this can be adapted to a surface mounted installation at the venue. And the other way around. . The surface mounted and suspended luminaire range fit to many different office spaces like open plan office, corridors, reception or meeting rooms. FlexBlend is offered in both lines and as standalone, using the same lighting module. This gives the option to the users to use FlexBlend as standalone now, and tomorrow, as line. The controller is integrated in the luminaire. As technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations that can help optimize operations further. For this reason, FlexBlend holds all connectivity and future ready options available. As System Ready luminaire it can be paired with lighting management systems such as the Philips SpaceWise, and to software-based lighting systems as Interact Office wired (PoE) and Interact Office wireless and/or existing and upcoming sensor innovations. The luminaire range is therefore future ready and can be delivered without any system component, and in a next phase, in the field to be upgraded. An attractive opportunity for new installations and renovations.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If The above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

FlexBlend, Suspended

Product data

General Information		Optical cover material	
Light source replaceable	No	Polymethyl methacrylate	
Number of gear units	1 unit	Fixation material	Stainless steel
Driver included	Yes	Housing Color	Silver
Service tag	Yes	Optical cover finish	Textured
Lighting Technology	LED	Overall length	1,470 mm
Value ladder	Performance	Overall width	200 mm
Warranty period	5 years	Overall height	73 mm
		Dimensions (Height x Width x Depth)	73 x 200 x 1470 mm
		Ingress protection code	IP20 [Finger-protected]
		Mech. impact protection code	IK02 [0.2 J standard]
		Mounting	Suspension set twin, triangle
		Net Weight (Piece)	5.314 kg
Approval and Application			
		Glow-wire test	Temperature 650 °C, duration 30 s
		Flammability mark	For mounting on normally flammable surfaces
		CE mark	Yes
		ENEC mark	ENEC plus mark
		Photobiological risk	Photobiological risk group 0 @200mm to EN62778
		EU RoHS compliant	Yes
		Performance ambient temperature Tq	25 °C
		Flickering value (PstLM) - Flickering value as 1 per EN 61000-3-3	
		Stroboscopic effect visibility measure (SVM)	0.4
		Ambient temperature range	+10 to +40 °C
Initial Performance (IEC Compliant)			
		Luminous flux tolerance	+/-10%
		Initial chromaticity	(0.38, 0.38) SDCM <3
		Power consumption tolerance	+/-10%
		Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3
Over Time Performance (IEC Compliant)			
		Control gear failure rate at median useful life 50000 h	5 %
		Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L85
		Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L75
Sustainability Data			
		Sustainability rating	Unclassified
		Serviceability class	Class B, luminaire is equipped with some serviceable parts (when applicable): driver, control units, surge protection device, front cover and mechanical parts
Light Technical			
Luminous Flux	4,500 lm		
Saturated Red (R9)	>50		
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	112 lm/W		
Color rendering index (CRI)	>90		
Beam angle of light source	120 degree(s)		
Light source color	940 neutral white		
Optic type	Wide beam		
Luminaire light beam spread	82° x 85°		
Unified glare rating CEN	19		
Operating and Electrical			
Input Voltage	220 to 240 V		
Line Frequency	50 to 60 Hz		
Initial CLO power consumption	- W		
Average CLO power consumption	- W		
Inrush current	25.1 A		
Inrush time	0.214 ms		
Power Consumption	42.5 W		
Power Factor (Fraction)	0.9		
Connection	Push-in connector 5-pole		
Cable	Cable 2.2 m (Eca class) without plug 5-pole		
Number of products on MCB of 16 A type B	15		
Suitable for random switching	Yes (relates to presence/ movement detection and daylight harvesting)		
Protection class IEC	Safety class I		
Controls and Dimming			
Dimmable	Yes		
Driver/power unit/transformer	Power supply unit with DALI interface		
Control interface	DALI		
Constant light output	No		
DALI Standard	DALI-2™		
Maximum dim level	1%		
Mechanical and Housing			
Housing Material	Steel		
Reflector material	Polycarbonate		
Optic material	Polycarbonate		


FlexBlend, Suspended

Product Data


Order product name	SP342P 45S/940 DEIA MLO SMT L150 SI
Full product name	SP342P 45S/940 DEIA MLO SMT L150 SI
Full product code	871951410374000
Order code	10374000
Material Nr. (12NC)	910925867113
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8719514103740
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514103740
Product family code	SP342P [FLEXBLEND SUSPENDEED D/I STAND-ALONE]

Dimensional drawing



Photometric data



Polar Normal (separate) - SM340CI - 910925867113

