



Pacific LED Gen5 Value

WT475C 107S/840 PSD WB L1800

Pacific LED Gen5 Value, Waterproof, 81 W, L1800 mm, 10700 lm, 4000 K, DALI, Wide beam, Clear, IP66, IK08

Waterproof, L1800 mm, Polycarbonate, White, Power supply unit with DALI interface, 10700 lm, 81 W, 132 lm/W, 4000 K, (0.38, 0.38) SDCM <3, Wide beam, Clear, Polycarbonate, IP66 | Dust penetration-protected, jet-proof, IK08 | 5 J vandal-protected, Safety class I, Push-in connector 5-pole

Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof seal and IP66 rating
- Do not install the luminaire in locations where it will be exposed to direct sunlight

Product data

General Information		Color rendering index (CRI)	
Light source replaceable	Yes		>80
Number of gear units	1 unit	Light source color	840 neutral white
Driver included	Yes	Optic type	Wide beam
Service tag	Yes	Luminaire light beam spread	93° x 93°
Lighting Technology	LED	Unified glare rating CEN	22
Value ladder	Specification	Operating and Electrical	
Warranty period	5 years	Input Voltage	220 to 240 V
Light Technical		Line Frequency	50 to 60 Hz
Luminous Flux	10,700 lm	Inrush current	25 A
Correlated Color Temperature (Nom)	4000 K	Inrush time	0.23 ms
Luminous Efficacy (rated) (Nom)	132 lm/W	Power Consumption	81 W
		Power Factor (Fraction)	0.99

Pacific LED Gen5 Value

Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	20
Suitable for random switching	No
Protection class IEC	Safety class I
Total harmonic distortion	5 %

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
DALI Standard	DALI-2™

Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	1,810 mm
Overall width	96 mm
Overall height	68 mm
Dimensions (Height x Width x Depth)	68 x 96 x 1810 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Net Weight (Piece)	3.100 kg

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC plus mark
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-25 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3

Power consumption tolerance	+/-11%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

Sustainability Data


Sustainability rating	Signify Circle
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.
Embedded carbon (A1-A3)	31.5 kg CO ₂ e
Product non-virgin material ratio	20.3 %
Recyclable content ratio of the finished product	62 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kWh)
GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) /lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO ₂ eq / kWh)
Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

Product Data


Order product name	WT475C 107S/840 PSD WB L1800
Full product name	WT475C 107S/840 PSD WB L1800
Full product code	871951462351400
Order code	910925868286
Material Nr. (12NC)	910925868286
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514623514
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514623514
Product family code	WT475C [Pacific LED gen5 Value]

Pacific LED Gen5 Value

Dimensional drawing



Photometric data



Polar Normal (separate) - WT475CI - 910925868286

