



Pacific LED Gen5

WT495C 80S/840 PSU WB PI5 L1800

Pacific LED Gen5, Waterproof, 49 W, L1800 mm, 8000 lm, 4000 K, Wide beam, Clear, IP66, IK08

The Pacific LED Gen5 WT490C series is an innovative and best-in-class LED waterproof luminaire that is praised for its optimal performance. It meets the demanding requirements of contemporary and harsh industries. It is a very robust, compact and reliable luminaire with excellent quality of light. With a high degree of mechanical (IK08), water and dust protection (IP66), combined with proven chemical resistance, the Pacific LED Gen5 WT490C can perfectly withstand the harsh conditions of the automotive, food and heavy industries. But it also performs well in car parks and warehouses. The Pacific LED Gen5 WT490C luminaires provide superior, artefact-free light quality and homogeneous light, offered with multiple optics and a broad range of light outputs (up to 15,000 lm). This ensures more flexibility in optimised light scheme planning. They are also designed with a circular approach, which means that these fully-serviceable luminaires can be upgraded to extend their overall lifecycle. The luminaires stand out because of their quick-and-easy installation that facilitates through wiring and various connection and mounting options. But also, because of their attractive TCO, energy efficiency and ease of maintenance – with minimum of disruption to operations in demanding applications. To make the Pacific LED Gen5 WT490C even more complete, system integration with Interact Industry opens up additional opportunities for optimised efficiency, energy savings, improved light management, productivity and safety. Making it future-proof in every way. Discover the Pacific LED Gen5 WT490C series. Optimal performance for demanding environments.

Warnings and Safety

- UV radiation will damage the material over time, resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Product data

Pacific LED Gen5

General Information	
Light source replaceable	Yes
Number of gear units	Unit
Driver included	Yes
Service Tag	Yes
Lighting Technology	LED
Value ladder	Specification
Serviceability class	Class A, the luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge-protection device, optics, front cover and mechanical parts
Warranty period	5 years
Sustainability rating	Signify Circle

Light Technical	
Luminous Flux	8,000 lm
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	157 lm/W
Colour rendering index (CRI)	>80
Light source colour	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	93° x 93°
Unified Glare Rating (CEN)	22

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	9 A
Inrush time	0.065 ms
Power Consumption	49 W
Power Factor (Fraction)	0.97
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB (16 A type B)	26
Suitable for random switching	No
Protection class IEC	Safety class I
Total harmonic distortion	20 %

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing	
Housing material	Polycarbonate
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Housing Colour	White

Optical cover/lens finish	Clear
Overall length	1,810 mm
Overall width	96 mm
Overall height	68 mm
Dimensions (height x width x depth)	68 x 96 x 1810 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Net Weight (Piece)	3.200 kg

Approval and Application	
Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC plus mark
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Ambient temperature range	-35 to +60 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80


Product Data	
Order product name	WT495C 80S/840 PSU WB P15 L1800
Full product name	WT495C 80S/840 PSU WB P15 L1800
Full EOC	871951462761100
Order code	910925868701
Material no. (12 NC)	910925868701
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514627611
Numerator – packs per outer box	1
EAN/UPC - Case	8719514627611

Pacific LED Gen5


Product family code

WT495C [Pacific LED gen5 XT]

Dimensional drawing



Photometric data



Polar Normal (separate) - WT490CI - 910925868701

