



AluRoad gen2

BGP025 LED113/740 II DM CLO-DDF2

AluRoad gen2, Road & street light, 61 W, 9030 lm, 4000 K, CRI70, Programmable (via DALI or NFC) stand-alone dimming, Distribution medium, Safety class II, IP66

The AluRoad gen2 family is available in 2 versions, standard AluRoad gen2 and AluRoad gen2 Pro. These are available in 2 sizes, Mini and Medium. Standard AluRoad gen2 as BGP020 Mini and BGP025 Medium, AluRoad gen2 Pro as BGP021 Mini and BGP026 Medium. Standard AluRoad gen2 features a fixed spigot for both post top 0 degrees tilt and side entry with limited negative tilt. AluRoad gen2 Pro is equipped with an adjustable spigot allowing tilt settings in both post top and side entry, positive and negative. AluRoad gen2 enables you to easily upgrade your city's lighting and enjoy the benefits of LED technology, designated to further minimize Total Cost of Investment and Ownership. The family is ideally suited for both new build areas and streets as well as renovation of existing installations. This affordable family not only offers a clean and timeless design to blend in with the environment, but also brings high quality lighting and future proof solutions with significant energy and maintenance savings over a long operational life.

Product data

General Information			
Lamp family code	LED113 [LED module 11300 lm]		board, driver, control units, surge protection device, optics, front cover and mechanical parts
Number of gear units	1 unit		
Driver included	Yes	Warranty period	5 years
Light source engine type	LED	Sustainability rating	Signify Circle
Service tag	Yes		
Value ladder	Performance	Light Technical	
Serviceability class	Class A, luminaire is equipped with serviceable parts (when applicable): LED	Upward light output ratio	0
		Luminous Flux	9,030 lm

AluRoad gen2

Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	153 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Luminaire light beam spread	5° x 55° x 150°
Optic type outdoor	Distribution medium
Effective projected area	0.032 m²

Sustainability Data

Embedded carbon (A1-A3)	33.7 kg CO _{2e}
Recyclable content ratio of the finished product	56.1 %
Product non-virgin material ratio	38.8 %
GWP total B6 (kg CO _{2eq}) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO _{2eq} / kwh)
GWP total B6 (kg CO _{2eq}) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO ₂ eq / kwh)

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	43 A
Inrush time	0.27 ms
Power Consumption	61 W
Power Factor (Fraction)	0.97
Connection	Push-in connector 2-pole
Cable	-
Number of products on MCB of 16 A type B	10
Protection class IEC	Safety class II
Surge Protection (Common/Differential)	Surge protection level until 6 kV differential mode and 8 kV common mode

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DynaDimmer and constant light output (integrated)
Control interface	Programmable (via DALI or NFC) stand-alone dimming
Constant light output	Yes
Embedded control	Constant light output and DynaDimmer fixed presets version 2

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Glass

Fixation material	Stainless steel
Housing Color	Gray
Mounting device	Side-entry for diameter 48 to 60 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	592 mm
Overall width	230 mm
Overall height	112 mm
Dimensions (Height x Width x Depth)	112 x 230 x 592 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Optical cover type	Flat glass
Net Weight (Piece)	4.400 kg

Approval and Application

Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-40 °C to 50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L98
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L95

Product Data

Order product name	BGP025 LED113/740 II DM CLO-DDF2
Full product name	BGP025 LED113/740 II DM CLO-DDF2
Full product code	871951476886400
Order code	910925869088
Material Nr. (12NC)	910925869088
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Product family code	BGP025 [AluRoad gen2 Medium]

AluRoad gen2

Dimensional drawing



Dimensions (mm)						
Luminaire	A	B	C	D	E	G
Mini BGPO20	447	70	112	111	334	88
Medium BGPO25	592	70	112	111	481	88

