



# Maxos fusion

## LL512T 4x2.5+2x1.5 Gen2 WH

### LL512T | Maxos fusion Rail

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

### Product data

General Information		Material	
Service tag	Yes	Material	Steel
Value ladder	Specification	Ingress protection code	IP20 [Finger-protected]
Operating and Electrical		Mech. impact protection code	IK02 [0.2 J standard]
Input Voltage	220 to 240 V	Accessory color	White
Line Frequency	50 to 60 Hz	Angle	-
Protection class IEC	Safety class I	Net Weight (Piece)	1.272 kg
Mechanical and Housing		Approval and Application	
Overall length	1,138 mm	CE mark	Yes
Overall width	62 mm	EU RoHS compliant	Yes
Overall height	42 mm	Product Data	
Dimensions (Height x Width x Depth)	42 x 62 x 1138 mm	Order product name	LL512T 4x2.5+2x1.5 Gen2 WH
		Full product name	LL512T 4x2.5+2x1.5 Gen2 WH

## Maxos fusion

Full product code	872016942516399
Order code	910925869411
Material Nr. (12NC)	910925869411
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169425163

Numerator - Packs per outer box	10
EAN/UPC - Case	8719514772014
Product family code	LL512T [Maxos fusion Rail]

### Dimensional drawing

