



# Maxos fusion

## LL500Z 2xEP CU Gen2 WH

LL500Z | Maxos fusion Acc.

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

### Product data

General Information		Material	
Service tag	Yes		Steel
Value ladder	Specification	Ingress protection code	IP20 [Finger-protected]
Operating and Electrical		Mech. impact protection code	IK02 [0.2 J standard]
Input Voltage	- V	Accessory color	White
Line Frequency	- Hz	Angle	-
Protection class IEC	-	Net Weight (Piece)	0.080 kg
Mechanical and Housing		Approval and Application	
Overall length	120 mm	CE mark	Yes
Overall width	100 mm	EU RoHS compliant	Yes
Overall height	50 mm	Product Data	
Dimensions (Height x Width x Depth)	50 x 100 x 120 mm	Order product name	LL500Z 2xEP CU Gen2 WH
		Full product name	LL500Z 2xEP CU Gen2 WH

## Maxos fusion

Full product code	872016942549199
Order code	910925869480
Material Nr. (12NC)	910925869480
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169425491

Numerator - Packs per outer box	6
EAN/UPC - Case	8719514772700
Product family code	LL500Z [Maxos fusion Acc.]

