



Maxos fusion

LL500Z CM L400 Gen2 WH

LL500Z | Maxos fusion Acc.

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Product data

General Information	
Service Tag	Yes
Value ladder	Specification
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class I
Mechanical and Housing	
Overall length	400 mm
Overall width	62 mm
Overall height	42 mm
Dimensions (height x width x depth)	42 x 62 x 400 mm

Material	Steel
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Accessory colour	White
Angle	-
Net Weight (Piece)	0.500 kg
Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes
Product Data	
Order product name	LL500Z CM L400 Gen2 WH
Full product name	LL500Z CM L400 Gen2 WH

Maxos fusion

Full EOC	871951477273100
Order code	910925869483
Material no. (12 NC)	910925869483
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514772731

Numerator – packs per outer box	1
EAN/UPC - Case	8719514772731
Product family code	LL500Z [Maxos fusion Acc.]

