



# Maxos fusion

## LL512X LED61S/840 SIA O-PC 7 WH HE

Maxos fusion, trunking light unit, 37 W, L1138 mm, 5200 lm, 4000 K, Wireless, Interact Ready, Opal, Opal, White

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

### Product data

General Information	
Number of gear units	1 unit
Driver included	Yes
Value ladder	Specification
Warranty period	5 years
Light Technical	
Luminous Flux	5,200 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	141 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)

Light source color	840 neutral white
Optic type	Opal
Luminaire light beam spread	180°
Unified glare rating CEN	22
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.28 ms
Power Consumption	37 W
Power Factor (Fraction)	0.98

## Maxos fusion

Connection	Connection unit 7-pole
Cable	-
Number of products on MCB of 16 A type B	21
Suitable for random switching	Not applicable
Protection class IEC	Safety class I

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Sensor ready driver Interact System ready
Control interface	Wireless
Constant light output	No
DALI Standard	DALI-2™ D4i™
Connectivity	Interact Ready

### Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Opal
Overall length	1,138 mm
Overall width	70 mm
Overall height	35 mm
Dimensions (Height x Width x Depth)	35 x 70 x 1138 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	1.380 kg

### Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +35 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.34, 0.35) SDCM <3
Power consumption tolerance	+/-11%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L95
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L85

### Sustainability Data


Sustainability rating	Signify Circle
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.
Embedded carbon (A1-A3)	13.7 kg CO <sub>2</sub> e
Product non-virgin material ratio	16.4 %
Recyclable content ratio of the finished product	54.9 %
GWP total B6 (kg CO <sub>2</sub> eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO <sub>2</sub> eq / kWh)
GWP total B6 (kg CO <sub>2</sub> eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO <sub>2</sub> eq / kWh)

### Product Data


Order product name	LL512X LED61S/840 SIA O-PC 7 WH HE
Full product name	LL512X LED61S/840 SIA O-PC 7 WH HE
Full product code	872016947385000
Order code	910925870058
Material Nr. (12NC)	910925870058
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169473850
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169473850
Product family code	LL512X [Maxos fusion Panel]

# Maxos fusion

## Dimensional drawing



## Photometric data



Polar Normal (separate) - LL500XI - 910925870058

