



# CoreLine trunking gen2.5

## LL243X 240S/840 UE DIA NB BV WH

CoreLine trunking gen2.5, Basic (stand alone) version, UltraEfficient, 128 W, L3400 mm, 24000 lm, 4000 K, DALI, Interact Ready, Narrow beam, Frosted, White, IP20

Basic (stand alone) version, UltraEfficient, L3400 mm, Steel, White, Traffic white (RAL9016), Dali dimming Interact System ready, 24000 lm, 128 W, 188 lm/W, 4000 K, (0.38, 0.38) SDCM <3, Narrow beam, Frosted, Polycarbonate, IP20 | Finger-protected, IK02 | 0.2 J standard, Safety class I, Push-in connector 5-pole

### Product data

General Information	
Number of gear units	2 units
Driver included	Yes
Value ladder	Performance
Warranty period	5 years
Light Technical	
Luminous Flux	24,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	188 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	Narrow beam
Luminaire light beam spread	35° x 71°

Unified glare rating CEN	22
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	25 A
Inrush time	230 ms
Power Consumption	128 W
Power Factor (Fraction)	0.97
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	20
Suitable for random switching	Not applicable

# CoreLine trunking gen2.5

Protection class IEC	Safety class I
Total harmonic distortion	20 %

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Dali dimming Interact System ready
Control interface	DALI
Constant light output	No
DALI Standard	DALI-2™ with extended data: Parts 251/252/253
Maximum dim level	1%
Connectivity	Interact Ready

## Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Frosted
Overall length	3,400 mm
Overall width	80 mm
Overall height	50 mm
Dimensions (Height x Width x Depth)	50 x 80 x 3400 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	4.980 kg

## Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC plus mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +35 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L85
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L75

## Sustainability Data


Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.
Embedded carbon (A1-A3)	32.3 kg CO <sub>2</sub> e
Product non-virgin material ratio	14.6 %
Recyclable content ratio of the finished product	55.7 %
GWP total B6 (kg CO <sub>2</sub> eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO <sub>2</sub> eq / kwh)
GWP total B6 (kg CO <sub>2</sub> eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) /lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO <sub>2</sub> eq / kwh)

## Product Data

Order product name	LL243X 240S/840 UE DIA NB BV WH
Full product name	LL243X 240S/840 UE DIA NB BV WH
Full product code	872016947477200
Order code	47477200
Material Nr. (12NC)	910925870151
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169474772
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169474772
Product family code	LL243X [Coreline trunking Gen2.5]

## CoreLine trunking gen2.5

### Dimensional drawing



### Photometric data



Polar Normal (separate) - LL240XI - 910925870151

