



Maxos unify

LL554T 4x2.5+2x1.5 Gen2 BK

LL554T | Maxos unify rail 4430mm, IP20 | Finger-protected

An adaptable LED trunking system, combining the well proven advantages of an electrical track which allows flexible positioning of linear panels offering multiple flux/ length combinations with specially designed lenses to direct the light where needed. A solution allowing for new projects to be designed with optimal number of linear panels and a solution for retrofitting old installations - Bringing your application right up to date with the latest lighting possibilities. Now, and in the future.

Product data

General Information	
Value ladder	Specification

Mechanical and Housing	
Overall height	42 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	5.500 kg

Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes

Product Data	
Order product name	LL554T 4x2.5+2x1.5 Gen2 BK
Full product name	LL554T 4x2.5+2x1.5 Gen2 BK
Full product code	872016996494599
Order code	910925870827
Material Nr. (12NC)	910925870827
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169964945
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169954809
Product family code	LL554T [Maxos unify rail 4430mm]

Maxos unify

Dimensional drawing

