



# Maxos unify

## LL552X 160S/840 NE SIA NB WH

Maxos unify, trunking light unit, 98 W, 2215 mm, 16000 lm, 4000 K, Wireless, Interact Ready, Narrow beam, Textured, White, IP20

trunking light unit, 2215 mm, Steel, White, Signal white (RAL9003), Sensor ready driver Interact System ready, 16000 lm, 98 W, 163 lm/W, 4000 K, (0.34. 0.35) SDCM <3, Narrow beam, Textured, Polymethyl methacrylate, IP20 | Finger-protected, IK03 | 0.3 J, Safety class I, Connection unit 7-pole

### Product data

General Information	
Number of gear units	1 unit
Driver included	Yes
Value ladder	Specification
Warranty period	5 years
Light Technical	
Luminous Flux	16,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	163 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	Narrow beam
Luminaire light beam spread	32° x 58°
Unified glare rating CEN	22
Operating and Electrical	
Input Voltage	220-240 V

Line Frequency	50 to 60 Hz
Inrush current	4.5 A
Inrush time	1 ms
Power Consumption	98 W
Power Factor (Fraction)	0.98
Connection	Connection unit 7-pole
Cable	-
Number of products on MCB of 16 A type B	18
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Total harmonic distortion	7 %
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Sensor ready driver Interact System ready
Control interface	Wireless
Constant light output	No
DALI Standard	DALI-2™

# Maxos unify

Maximum dim level	1%
Connectivity	Interact Ready

## Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Steel
Housing Color	White
Optical cover finish	Textured
Overall length	2,215 mm
Overall width	62 mm
Overall height	14 mm
Dimensions (Height x Width x Depth)	14 x 62 x 2215 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Net Weight (Piece)	2.460 kg

## Emergency Operation

Central Emergency	No
Emergency lighting	-

## Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +35 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.34, 0.35) SDCM <3
Power consumption tolerance	+/-11%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %

Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L95
---------------------------------------------------------------------	-----

Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L85
----------------------------------------------------------------------	-----

## Sustainability Data

Sustainability rating	Signify Circle
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.

Embedded carbon (A1-A3)	14.5 kg CO <sub>2</sub> e
-------------------------	---------------------------

Product non-virgin material ratio	14.8 %
-----------------------------------	--------

Recyclable content ratio of the finished product	51.8 %
--------------------------------------------------	--------

GWP total B6 (kg CO <sub>2</sub> eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO <sub>2</sub> eq / kWh)
----------------------------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------

GWP total B6 (kg CO <sub>2</sub> eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO <sub>2</sub> eq / kWh)
------------------------------------------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Non-virgin material ratio of the packaging	Cardboard > 80% recycled
--------------------------------------------	--------------------------

Packaging Recyclable content ratio	Cardboard recycling rate > 80%
------------------------------------	--------------------------------

Packaging Material	Cardboard
--------------------	-----------

## Product Data

Order product name	LL552X 160S/840 NE SIA NB WH
--------------------	------------------------------

Full product name	LL552X 160S/840 NE SIA NB WH
-------------------	------------------------------

Full product code	872016995508000
-------------------	-----------------

Order code	910925870855
------------	--------------

Material Nr. (12NC)	910925870855
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

EAN/UPC - Product/Case	8720169955080
------------------------	---------------


Numerator - Packs per outer box	1
---------------------------------	---

EAN/UPC - Case	8720169955080
----------------	---------------

Product family code	LL552X [Maxos unify panel 2215mm]
---------------------	-----------------------------------

# Maxos unify

## Dimensional drawing



## Photometric data



Polar Normal (separate) - LL550XI - 910925870855

