



Maxos unify

LL552X 100S/840 UE SIA WB WH

Maxos unify, trunking light unit, UltraEfficient, 51 W, 2215 mm, 10000 lm, 4000 K, Wireless, Interact Ready, Wide beam, Textured, White, IP20

trunking light unit, UltraEfficient, 2215 mm, Steel, White, Signal white (RAL9003), Sensor ready driver Interact System ready, 10000 lm, 51 W, 196 lm/W, 4000 K, (0.34. 0.35) SDCM <3, Wide beam, Textured, Polymethyl methacrylate, IP20 | Finger-protected, IK03 | 0.3 J, Safety class I, Connection unit 7-pole

Product data

General Information	
Number of gear units	1 unit
Driver included	Yes
Value ladder	Specification
Warranty period	5 years
Light Technical	
Luminous Flux	10,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	196 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	57° x 76°
Unified glare rating CEN	22

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	25 A
Inrush time	0.280 ms
Power Consumption	51 W
Power Factor (Fraction)	0.98
Connection	Connection unit 7-pole
Cable	-
Number of products on MCB of 16 A type B	21
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Total harmonic distortion	5 %
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Sensor ready driver Interact System ready

Maxos unify

Control interface	Wireless
Constant light output	No
DALI Standard	DALI-2™
Maximum dim level	1%
Connectivity	Interact Ready

Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Steel
Housing Color	White
Optical cover finish	Textured
Overall length	2,215 mm
Overall width	62 mm
Overall height	14 mm
Dimensions (Height x Width x Depth)	14 x 62 x 2215 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Net Weight (Piece)	2.460 kg

Emergency Operation

Central Emergency	No
Emergency lighting	-

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.34, 0.35) SDCM <3
Power consumption tolerance	+/-11%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
---	-----

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L95
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L85

Sustainability Data


Sustainability rating	Signify Circle
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.
Embedded carbon (A1-A3)	14.5 kg CO _{2e}
Product non-virgin material ratio	14.8 %
Recyclable content ratio of the finished product	51.8 %
GWP total B6 (kg CO _{2eq}) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO _{2eq} / kWh)
GWP total B6 (kg CO _{2eq}) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO _{2eq} / kWh)
Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

Product Data


Order product name	LL552X 100S/840 UE SIA WB WH
Full product name	LL552X 100S/840 UE SIA WB WH
Full product code	872016995510300
Order code	910925870857
Material Nr. (12NC)	910925870857
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169955103
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169955103
Product family code	LL552X [Maxos unify panel 2215mm]

Maxos unify

Dimensional drawing



Photometric data



Polar Normal (separate) - LL550XI - 910925870857

