


LL550E MPL Gen2 WH

910925870977



Maxos unify, Accessory

An adaptable LED trunking system, combining the well proven advantages of an electrical track which allows flexible positioning of linear panels offering multiple flux/ length combinations with specially designed lenses to direct the light where needed. A solution allowing for new projects to be designed with optimal number of linear panels and a solution for retrofitting old installations - Bringing your application right up to date with the latest lighting possibilities. Now, and in the future.

General Information

Value ladder	Specification
--------------	---------------

Operating and Electrical

Input Voltage	222 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class I

Mechanical and Housing

Overall length	213 mm
Overall width	96 mm
Overall height	111 mm
Dimensions (Height x Width x Depth)	111 x 96 x 213 mm
Material	Steel
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Accessory color	White
Net Weight (Piece)	0.800 kg

Approval and Application


CE mark	Yes
EU RoHS compliant	Yes

Product Data

Order product name	LL550E MPL Gen2 WH
Full product name	LL550E MPL Gen2 WH

Full product code	872016995629200
Order code	95629200
Material Nr. (12NC)	910925870977
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169956292
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169956292
Product family code	LL550E [Maxos unify electrical accessories]

Dimensional drawing



Integrated Sensor

Sensor Image English	Sensor Code	Sensor Name	Website
	913701071303	MPS3210/05 OCC-DL IA DALI WH 6M S	Product Website

Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	MI-LL550E-MPS.pdf	Download

