



Maxos unify

LL550E MPL Gen2 WH

Maxos unify, Accessory

An adaptable LED trunking system, combining the well proven advantages of an electrical track which allows flexible positioning of linear panels offering multiple flux/ length combinations with specially designed lenses to direct the light where needed. A solution allowing for new projects to be designed with an optimal number of linear panels and a solution for retrofitting old installations – Bringing your application right up to date with the latest lighting possibilities. Now and in the future.

Product data

General Information	
Value ladder	Specification
Operating and Electrical	
Input Voltage	222 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class I
Mechanical and Housing	
Overall length	213 mm
Overall width	96 mm
Overall height	111 mm
Dimensions (height x width x depth)	111 x 96 x 213 mm
Material	Steel
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Accessory colour	White

Net Weight (Piece)	0.800 kg
Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes
Product Data	
Order product name	LL550E MPL Gen2 WH
Full product name	LL550E MPL Gen2 WH
Full EOC	872016995629200
Order code	910925870977
Material no. (12 NC)	910925870977
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8720169956292
Numerator – packs per outer box	1
EAN/UPC - Case	8720169956292
Product family code	LL550E [Maxos unify electrical accessories]

Dimensional drawing

