

LL500E MPM Gen2 WH

910925870980



Maxos fusion, Accessory

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

General Information

Value ladder	Specification
--------------	---------------

Operating and Electrical

Input Voltage	222 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class I

Mechanical and Housing

Overall length	213 mm
Overall width	96 mm
Overall height	111 mm
Dimensions (height x width x depth)	111 x 96 x 213 mm
Material	Steel
Ingress protection code	IP20 [Finger-protected]

Mech. impact protection code	IK02 [0.2 J standard]
Accessory colour	White
Net Weight (Piece)	0.800 kg


Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Product Data

Order product name	LL500E MPM Gen2 WH
Full product name	LL500E MPM Gen2 WH

Dimensional drawing



Integrated Sensor

Sensor Image	Sensor Code	Sensor Name	Website
	913701071403	MPS3220/05 OCC-DL IA DALI WH 12M S	Product Website ↗

Related Documents

Documents and certificates	Document Name	Download
Tender text	Tender_Text_910925870980_en_GB.txt	Download 📄
Installation Instructions	MI-LL500E-MPS.pdf	Download 📄