



Maxos fusion

LL500E MPH Gen2 WH

Maxos fusion, Accessory

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Product data

General Information	
Value ladder	Specification
Operating and Electrical	
Input Voltage	222 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class I
Mechanical and Housing	
Overall length	213 mm
Overall width	96 mm
Overall height	111 mm
Dimensions (height x width x depth)	111 x 96 x 213 mm
Material	Steel

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Accessory colour	White
Net Weight (Piece)	0.800 kg
Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes
Product Data	
Order product name	LL500E MPH Gen2 WH
Full product name	LL500E MPH Gen2 WH
Full EOC	872016995633900
Order code	910925870981

Maxos fusion

Material no. (12 NC)	910925870981
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8720169956339
Numerator – packs per outer box	1

EAN/UPC - Case	8720169956339
Product family code	LL500E [Maxos fusion Electrical]

Dimensional drawing

