



Maxos unify

LL551X 40S/840 NE DIA VWB WH

Maxos unify, trunking light unit, 24 W, 1478 mm, 4000 lm, 4000 K, DALI, Interact Ready, Very wide beam, Textured, White, IP20

trunking light unit, 1478 mm, Steel, White, Signal white (RAL9003), Dali dimming Interact System ready, 4000 lm, 24 W, 163 lm/W, 4000 K, (0.34. 0.35) SDCM <3, Very wide beam, Textured, Polymethyl methacrylate, IP20 | Finger-protected, IK03 | 0.3 J, Safety class I, Connection unit 7-pole

Product data

General Information	
Number of gear units	1 unit
Driver included	Yes
Value ladder	Specification
Warranty period	5 years
Light Technical	
Luminous Flux	4,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	163 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	Very wide beam
Luminaire light beam spread	124° x 110°
Unified glare rating CEN	28
Operating and Electrical	
Input Voltage	220-240 V

Line Frequency	50 to 60 Hz
Inrush current	36 A
Inrush time	0.130 ms
Power Consumption	24 W
Power Factor (Fraction)	0.98
Connection	Connection unit 7-pole
Cable	-
Number of products on MCB of 16 A type B	25
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Total harmonic distortion	5 %
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Dali dimming Interact System ready
Control interface	DALI
Constant light output	No
DALI Standard	DALI-2™

Maxos unify

Maximum dim level	1%
Connectivity	Interact Ready

Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Steel
Housing Color	White
Optical cover finish	Textured
Overall length	1,478 mm
Overall width	62 mm
Overall height	14 mm
Dimensions (Height x Width x Depth)	14 x 62 x 1478 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Net Weight (Piece)	1.560 kg

Emergency Operation

Central Emergency	No
Emergency lighting	-

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.34, 0.35) SDCM <3
Power consumption tolerance	+/-11%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
---------------------------------------------------------	-----

Control gear failure rate at median useful life 100000 h	10 %
----------------------------------------------------------	------

Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L95
---------------------------------------------------------------------	-----

Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L85
----------------------------------------------------------------------	-----

Sustainability Data

Sustainability rating	Signify Circle
-----------------------	----------------

Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.
--------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Embedded carbon (A1-A3)	10.5 kg CO ₂ e
-------------------------	---------------------------

Product non-virgin material ratio	14.7 %
-----------------------------------	--------

Recyclable content ratio of the finished product	50.6 %
--------------------------------------------------	--------

GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kWh)
----------------------------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------

GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO ₂ eq / kWh)
------------------------------------------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------


Packaging Material	Cardboard
--------------------	-----------

Product Data


Order product name	LL551X 40S/840 NE DIA VWB WH
Full product name	LL551X 40S/840 NE DIA VWB WH
Full product code	872016995673500
Order code	910925871022
Material Nr. (12NC)	910925871022
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169956735
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169956735
Product family code	LL551X [Maxos unify panel 1478mm]

Maxos unify

Dimensional drawing



Photometric data



Polar Normal (separate) - 910925871022

