



# Maxos unify

## LL551X 133S/840 HE DIA WB WH

Maxos unify, trunking light unit, High efficiency, 73 W, 1478 mm, 13300 lm, 4000 K, DALI, Interact Ready, Wide beam, Textured, White, IP20

trunking light unit, High efficiency, 1478 mm, Steel, White, Signal white (RAL9003), Dali dimming Interact System ready, 13300 lm, 73 W, 182 lm/W, 4000 K, (0.34 0.35) SDCM <3, Wide beam, Textured, Polymethyl methacrylate, IP20 | Finger-protected, IK03 | 0.3 J, Safety class I, Connection unit 7-pole

### Product data

General Information	
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes
Value ladder	Specification
Warranty period	5 years
Light Technical	
Luminous Flux	13,300 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	182 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	57° x 76°
Unified glare rating CEN	25

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	25 A
Inrush time	0.230 ms
Power Consumption	73 W
Power Factor (Fraction)	0.98
Connection	Connection unit 7-pole
Cable	-
Number of products on MCB of 16 A type B	20
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Total harmonic distortion	5 %
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Dali dimming Interact System ready

# Maxos unify

Control interface	DALI
Constant light output	No
DALI Standard	DALI-2™
Maximum dim level	1%
Connectivity	Interact Ready

## Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Steel
Housing Color	White
Optical cover finish	Textured
Overall length	1,478 mm
Overall width	62 mm
Overall height	14 mm
Dimensions (Height x Width x Depth)	14 x 62 x 1478 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Net Weight (Piece)	1.560 kg

## Emergency Operation

Central Emergency	No
Emergency lighting	-

## Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +35 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.34. 0.35) SDCM <3
Power consumption tolerance	+/-11%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
---	-----

Control gear failure rate at median useful life 100000 h	10 %
--	------

Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L95
---	-----

Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L85
--	-----

## Sustainability Data

Sustainability rating	Signify Circle
-----------------------	----------------

Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.
--------------	---

Embedded carbon (A1-A3)	10.5 kg CO <sub>2</sub> e
-------------------------	---------------------------

Product non-virgin material ratio	14.7 %
-----------------------------------	--------

Recyclable content ratio of the finished product	50.6 %
--	--------

GWP total B6 (kg CO <sub>2</sub> eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO <sub>2</sub> eq / kWh)
--	--

GWP total B6 (kg CO <sub>2</sub> eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO <sub>2</sub> eq / kWh)
--	---

Non-virgin material ratio of the packaging	Cardboard > 80% recycled
--	--------------------------

Packaging Recyclable content ratio	Cardboard recycling rate > 80%
------------------------------------	--------------------------------

Packaging Material	Cardboard
--------------------	-----------

## Product Data

Order product name	LL551X 133S/840 HE DIA WB WH
--------------------	------------------------------

Full product name	LL551X 133S/840 HE DIA WB WH
-------------------	------------------------------

Full product code	872016995681000
-------------------	-----------------

Order code	910925871029
------------	--------------

Material Nr. (12NC)	910925871029
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

EAN/UPC - Product/Case	8720169956810
------------------------	---------------


Numerator - Packs per outer box	1
---------------------------------	---

EAN/UPC - Case	8720169956810
----------------	---------------


Product family code	LL551X [Maxos unify panel 1478mm]
---------------------	-----------------------------------

# Maxos unify

## Dimensional drawing



## Photometric data



Polar Normal (separate) - 910925871029

