



# Cleanroom LED CR250B

## CR250Z SMB W60L60

Cleanroom LED CR250B, Accessory, Steel, White

In applications where hygiene is crucially important, such as hospitals and food production facilities, customers want proven IP65 and IP54-rated luminaires that are safe to use and come at an attractive price. This family of Philips Cleanroom CR250B fixtures represent true value for money: the Philips LED engine delivers reliable, high-quality light, and the flexible mounting possibilities mean that this cleanroom LED lighting family can be used in a wide range of applications. These cleanroom luminaires are also compliant with all relevant standards (CE, EMC, RoHS).

### Product data

General Information		Approval and Application	
Value ladder	Performance	Angle	-
		Net Weight (Piece)	4.500 kg
Operating and Electrical		Sustainability Data	
Protection class IEC	-	CE mark	Yes
		EU RoHS compliant	Yes
Mechanical and Housing		Non-virgin material ratio of the packaging	
Overall length	630 mm	Cardboard > 80% recycled Plastic >35% recycled	
Overall width	630 mm	Packaging Recyclable content ratio	
Overall height	185 mm	Cardboard recycling rate > 80% Plastic recycling rate > 40%	
Dimensions (Height x Width x Depth)	185 x 630 x 630 mm	Packaging Material	
Material	Steel	Cardboard Plastic	
Ingress protection code	IP20 [Finger-protected]		
Mech. impact protection code	IK03 [0.3 J]		
Accessory color	White		

## Cleanroom LED CR250B

Product Data	
Order product name	CR250Z SMB W60L60
Full product name	CR250Z SMB W60L60
Full product code	871869607295000
Order code	07295000
Material Nr. (12NC)	910930030418

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696072950
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696072950

