

CR250Z SMB W60L60

910930030418



Cleanroom LED CR250B, Accessory, Steel, White

In applications where hygiene is crucially important, such as hospitals and food production facilities, customers want proven IP65- and IP54-rated luminaires that are safe to use and are an economical investment. This family of fixtures represents an affordable solution: the Philips LED engine delivers reliable, high-quality light, and the flexible mounting possibilities mean that this family can be used in a wide range of applications. The fixtures are also compliant with all relevant standards (CE, EMC, RoHS).

General Information

Value ladder	Performance
Operating and Electrical	
Protection class IEC	-

Mechanical and Housing

Overall length	630 mm
Overall width	630 mm
Overall height	185 mm
Dimensions (height x width x depth)	185 x 630 x 630 mm
Material	Steel
Ingress protection code	IP20 [Finger-protected]

Mech. impact protection code	IK03 [0.3 J]
Accessory colour	White
Angle	-
Net Weight (Piece)	4.500 kg

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Product Data

Order product name	CR250Z SMB W60L60
Full product name	CR250Z SMB W60L60
Full EOC	871869607295000
Order code	910930030418
Material no. (12 NC)	910930030418
Numerator – quantity per pack	1
EAN/UPC — Product/Case	8718696072950
Numerator – packs per outer box	1
EAN/UPC - Case	8718696072950

Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	Cleanroom_LED-CR250Z-II.pdf	Download 