



Cleanroom LED CR250B

CR250Z SMB W60L60

Cleanroom LED CR250B, Accessory, Steel, White

In applications where hygiene is crucially important, such as hospitals and food production facilities, customers want proven IP65 and IP54-rated luminaires that are safe to use and come at an attractive price. This family of Philips Cleanroom CR250B fixtures represents true value for money: the Philips LED engine delivers reliable, high-quality light, and the flexible mounting possibilities mean that this cleanroom LED lighting family can be used in a wide range of applications. These cleanroom luminaires are also compliant with all relevant standards (CE, EMC, RoHS).

Product data

General Information		Angle	
Value ladder	Performance	Net Weight (Piece)	4.500 kg
Operating and Electrical		Approval and Application	
Protection class IEC	-	CE mark	Yes
Mechanical and Housing		EU RoHS compliant	Yes
Overall length	630 mm	Product Data	
Overall width	630 mm	Order product name	CR250Z SMB W60L60
Overall height	185 mm	Full product name	CR250Z SMB W60L60
Dimensions (height x width x depth)	185 x 630 x 630 mm	Full EOC	871869607295000
Material	Steel	Order code	910930030418
Ingress protection code	IP20 [Finger-protected]	Material no. (12 NC)	910930030418
Mech. impact protection code	IK03 [0.3 J]	Local order code	CR250ZSW60
Accessory colour	White	Numerator – quantity per pack	1

Cleanroom LED CR250B

EAN/UPC — Product/Case	8718696072950
Numerator – packs per outer box	1
EAN/UPC - Case	8718696072950

