



Cleanroom LED CR250B, Accessory, Steel, White

In applications where hygiene is crucially important, such as hospitals and food production facilities, customers want proven IP65- and IP54-rated luminaires that are safe to use and are an economical investment. This family of fixtures represents an affordable solution: the Philips LED engine delivers reliable, high-quality light, and the flexible mounting possibilities mean that this family can be used in a wide range of applications. The fixtures are also compliant with all relevant standards (CE, EMC, RoHS).

General Information

Value ladder	Performance
Operating and Electrical	
Protection class IEC	-

Mechanical and Housing

Overall length	1,230 mm
Overall width	330 mm
Overall height	190 mm
Dimensions (height x width x depth)	190 x 330 x 1230 mm
Material	Steel
Ingress protection code	IP20 [Finger-protected]

Mech. impact protection code	IK03 [0.3 J]
Accessory colour	White
Angle	-
Net Weight (Piece)	5.000 kg

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Product Data

Order product name	CR250Z SMB W30L120
Full product name	CR250Z SMB W30L120
Full EOC	871869607296700
Order code	910930030518
Material no. (12 NC)	910930030518
Numerator – quantity per pack	1
EAN/UPC — Product/Case	8718696072967
Numerator – packs per outer box	1
EAN/UPC - Case	8718696072967

Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	Cleanroom_LED-CR250Z-II.pdf	Download 