



# GreenPerform Canopy Mini500 G4

## BBP500 G4 LED180/CW GU5.3 S-MB

GreenPerform Canopy Mini500 G4, 122 W, 18066 lm, 6500 K

The Philips GreenPerform Canopy Mini500 Gen4 lives up to the GreenPerform family's enviable reputation for reliable performance. Not only does this next-generation, energy-saving LED deliver leading system efficacy and extended long-term quality, it also offers a versatile selection of optics, connectivity, controls and installation options. So you can create the ideal lighting conditions for any space, at any time. The GreenPerform Canopy portfolio also includes a series that is ideal for canopy lighting in food applications. For professionals who demand high-performance, connected lighting for their lighting installations, this robust, optimized, and versatile family of LED canopy luminaires is the perfect choice for both indoor and outdoor canopy applications.

### Product data

General Information		Operating and Electrical	
Light source engine type	LED	Input Voltage	220-240 V
Service tag	Yes	Line Frequency	50 to 60 Hz
Value ladder	Performance	Inrush current	35.4 A
Light Technical		Power Consumption	122 W
Luminous Flux	18,066 lm	Power Factor (Fraction)	0.95
Correlated Color Temperature (Nom)	6500 K	Number of products on MCB of 16 A type B	8
Luminous Efficacy (rated) (Nom)	148 lm/W	Protection class IEC	Safety class I
Color rendering index (CRI)	>80	Controls and Dimming	
Light source color	865 cool daylight	Dimmable	No

# GreenPerform Canopy Mini500 G4

Control interface	-
-------------------	---

## Mechanical and Housing

Housing Material	Aluminium die-cast ADC1 - alloy grade (EN AC-47100)
Optical cover material	Tempered glass
Housing Color	White
Optical cover finish	Clear
Overall length	427 mm
Overall width	400 mm
Overall height	120 mm
Dimensions (Height x Width x Depth)	120 x 400 x 427 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Optical cover type	Clear glass
Net Weight (Piece)	6.590 kg

## Approval and Application

Flammability mark	For mounting on normally flammable surfaces
-------------------	---

CE mark	Yes
Ambient temperature range	-40 to +50 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

## Product Data

Order product name	BBP500 G4 LED180/CW GU5.3 S-MB
Full product name	BBP500 G4 LED180/CW GU5.3 S-MB
Full product code	872016954756800
Order code	54756800
Material Nr. (12NC)	911401500142
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169547568
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169547568

## Dimensional drawing

