



GreenUp Linear Flex

SP309P P48UD/830 L120W5 PSR 1-10V HD 2

GreenUp Linear Flex, 85 lm/W, 830 warm white, depends on driver (1-10V, DALI...)

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Linear Flex is a comprehensive product family which offers a variety of combinations between decorative and functional lighting units. It supports every of your desires with flexible linear family including suspension and recessed installations.

Product data

General Information		Protection class IEC	
Light source engine type	LED		Safety class I
Value ladder	Value		
Light Technical		Controls and Dimming	
Luminous Flux	4,100 lm	Dimmable	Yes
Correlated Color Temperature (Nom)	3000 K	Control interface	depends on driver (1-10V, DALI...)
Luminous Efficacy (rated) (Nom)	85 lm/W	Mechanical and Housing	
Color rendering index (CRI)	>80	Housing Material	Aluminum extruded
Light source color	830 warm white	Optical cover material	Polycarbonate
Operating and Electrical		Housing Color	Black
Input Voltage	220-240 V	Optical cover finish	Frosted
Line Frequency	50 or 60 Hz	Ingress protection code	IP20 [Finger-protected]
Power Consumption	48 W	Mech. impact protection code	IK03 [0.3 J]
Power Factor (Fraction)	0.9	Optical cover type	Linear-lens array oval shape
Number of products on MCB of 16 A type B 43		Net Weight (Piece)	2.790 kg
		Approval and Application	
		CE mark	No

GreenUp Linear Flex

Ambient temperature range	-20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	SP309P P48UD/830 L120W5 PSR 1-10V HD 2
Full product name	SP309P P48UD/830 L120W5 PSR 1-10V HD 2

Full product code	872016953184099
Order code	53184099
Material Nr. (12NC)	911401500732
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169531840
Numerator - Packs per outer box	3
EAN/UPC - Case	8720169543331

Dimensional drawing

