



# GreenPerform Canopy Mini500 G4

## BCP500 G4 LED85/NW PSD A-WB

GreenPerform Canopy Mini500 G4, 58 W, 8496 lm, 4000 K, DALI

The Philips GreenPerform Canopy Mini500 Gen4 lives up to the GreenPerform family's enviable reputation for reliable performance. Not only does this next-generation, energy-saving LED deliver leading system efficacy and extended long-term quality, it also offers a versatile selection of optics, connectivity, controls and installation options. So you can create the ideal lighting conditions for any space, at any time. The GreenPerform Canopy portfolio also includes a series that is ideal for canopy lighting in food applications. For professionals who demand high-performance, connected lighting for their lighting installations, this robust, optimized, and versatile family of LED canopy luminaires is the perfect choice for both indoor and outdoor canopy applications.

### Product data

General Information		Light source color	
Light source engine type	LED	840 neutral white	
Service tag	Yes	Operating and Electrical	
Value ladder	Performance	Input Voltage	220-240 V
<b>Light Technical</b>		Line Frequency	50 to 60 Hz
Luminous Flux	8,496 lm	Inrush current	35.4 A
Correlated Color Temperature (Nom)	4000 K	Power Consumption	58 W
Luminous Efficacy (rated) (Nom)	147 lm/W	Power Factor (Fraction)	0.9
Color rendering index (CRI)	>80	Number of products on MCB of 16 A type B 8	
		Protection class IEC	Safety class I

# GreenPerform Canopy Mini500 G4

## Controls and Dimming

Dimmable	DALI
Control interface	DALI

## Mechanical and Housing

Housing Material	Aluminium die-cast ADC1 - alloy grade (EN AC-47100)
Optical cover material	Tempered glass
Housing Color	White
Optical cover finish	Clear
Overall length	335 mm
Overall width	335 mm
Overall height	153 mm
Dimensions (Height x Width x Depth)	153 x 335 x 335 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Optical cover type	Clear glass
Net Weight (Piece)	7.290 kg

## Approval and Application

Flammability mark	For mounting on normally flammable surfaces
-------------------	---

CE mark	Yes
Ambient temperature range	-40 to +50 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

## Product Data

Order product name	BCP500 G4 LED85/NW PSD A-WB
Full product name	BCP500 G4 LED85/NW PSD A-WB
Full product code	872016954726100
Order code	911401505342
Material Nr. (12NC)	911401505342
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169547261
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169547261

## Dimensional drawing

