



# LuxSpace Pro

## DN592X LED26/CED P26PSD D150 WB G2

LuxSpace Pro, 25.7 W, 2630 lm, Tunable white 2700–6500 K, DALI

Philips LuxSpace Pro builds on the LuxSpace family's reputation for superb performance, extremely low energy use, high visual comfort and appearance design. This next generation of reliable LED downlights comes in an elegant design with a deep, recessed architecture and increased reflector depth to highlight the smallest of details. LuxSpace Pro is also a shining example of versatility. This energy-saving LED downlight is available in a comprehensive range of configurations from 450 to 8,000 lumen, 3inch to 8inch, with the option to choose fixed, dimmable, or Interact Ready variants. This makes LuxSpace Pro the perfect 'mix and match' solution for potentially broad and extended applications that require different lighting ambiances, with one cohesive luminaire look and feel.

### Product data

General Information		Unified glare rating CEN	
Light source engine type	LED		19
Service tag	Yes	Operating and Electrical	
Value ladder	Specification	Input Voltage	220 to 240 V
		Line Frequency	50 or 60 Hz
Light Technical		Power Consumption	25.7 W
Luminous Flux	2,630 lm	Power Factor (Fraction)	0.9
Correlated Color Temperature (Nom)	Tunable white 2700-6500 K	Number of products on MCB of 16 A type B	104
Luminous Efficacy (rated) (Nom)	102 lm/W	Protection class IEC	Safety class II
Color rendering index (CRI)	>80	Controls and Dimming	
Light source color	Tunable White Bio-up Cyan Enhanced Spectrum CR180	Dimmable	DALI
Optic type	Beam angle 60°		

# LuxSpace Pro

Control interface	DALI
<b>Mechanical and Housing</b>	
Housing Material	Aluminum Alloy
Optic material	Aluminum
Optical cover material	Polycarbonate
Housing Color	White
Optical cover finish	Matte
Overall height	100 mm
Overall diameter	162 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.35 J reinforced]
Optical cover type	Polycarbonate Diffuser
Net Weight (Piece)	0.600 kg
<b>Approval and Application</b>	
CE mark	Yes

Ambient temperature range	-20 to +40 °C
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	DN592X LED26/CED P26PSD D150 WB G2
Full product name	DN592X LED26/CED P26PSD D150 WB G2
Order code	911401506244
Material Nr. (12NC)	911401506244
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing

