



# GreenPerform Canopy Mini500 G4

## BCP500 G4 LED125/NW GU5.3 S-WB

GreenPerform Canopy Mini500 G4, 79 W, 12638 lm, 4000 K

The Philips GreenPerform Canopy Mini500 Gen4 lives up to the GreenPerform family's enviable reputation for reliable performance. Not only does this next-generation, energy-saving LED deliver leading system efficacy and extended long-term quality, it also offers a versatile selection of optics, connectivity, controls and installation options. So you can create the ideal lighting conditions for any space, at any time. The GreenPerform Canopy portfolio also includes a series that is ideal for canopy lighting in food applications. For professionals who demand high-performance, connected lighting for their lighting installations, this robust, optimized, and versatile family of LED canopy luminaires is the perfect choice for both indoor and outdoor canopy applications.

### Product data

General Information	
Light source engine type	LED
Service tag	Yes
Value ladder	Performance

  

Light Technical	
Luminous Flux	12,638 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	159 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	35.4 A
Power Consumption	79 W
Power Factor (Fraction)	0.95
Number of products on MCB of 16 A type B 8	
Protection class IEC	Safety class I

  

Controls and Dimming	
Dimmable	No

# GreenPerform Canopy Mini500 G4

Control interface	-
<b>Mechanical and Housing</b>	
Housing Material	Aluminium die-cast ADC1 - alloy grade (EN AC-47100)
Optical cover material	Tempered glass
Housing Color	White
Optical cover finish	Clear
Overall length	335 mm
Overall width	335 mm
Overall height	158 mm
Dimensions (Height x Width x Depth)	158 x 335 x 335 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Optical cover type	Clear glass
Net Weight (Piece)	6.690 kg
<b>Approval and Application</b>	
Flammability mark	For mounting on normally flammable surfaces

CE mark	Yes
Ambient temperature range	-40 to +50 °C
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	BCP500 G4 LED125/NW GU5.3 S-WB
Full product name	BCP500 G4 LED125/NW GU5.3 S-WB
Full product code	872016954843500
Order code	54843500
Material Nr. (12NC)	911401508142
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169548435
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169548435

## Dimensional drawing

