



# GreenPerform Panel RC099V G3

## RC099V G3 LED49/865 PSU W30L120

GreenPerform Panel RC099V G3, 120 lm/W, 865 cool daylight

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600, 300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

### Product data

General Information		Power Factor (Fraction)		0.9
Light source engine type	LED	Number of products on MCB of 16 A type B	17	
Service tag	Yes	Protection class IEC	Safety class II	
Value ladder	Performance			
Light Technical		Controls and Dimming		
Luminous Flux	4,800 lm	Dimmable	No	
Correlated Color Temperature (Nom)	6500 K	Control interface	-	
Luminous Efficacy (rated) (Nom)	120 lm/W			
Color rendering index (CRI)	>80	Mechanical and Housing		
Light source color	865 cool daylight	Housing Material	Metal	
Unified glare rating CEN	Not applicable	Optical cover material	Polystyrene	
		Housing Color	White RAL 9003	
Operating and Electrical		Optical cover finish	Opal	
Input Voltage	220-240 V	Ingress protection code	IP20 [Finger-protected]	
Line Frequency	50 or 60 Hz	Mech. impact protection code	IK03 [0.3 J]	
Power Consumption	40 W	Optical cover type	Opal	

## GreenPerform Panel RC099V G3

Net Weight (Piece)	2.000 kg
--------------------	----------

### Approval and Application

CE mark	Yes
Ambient temperature range	-20 °C to 45 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

### Product Data

Order product name	RC099V G3 LED49/865 PSU W30L120
--------------------	---------------------------------

Full product name	RC099V G3 LED49/865 PSU W30L120
Full product code	692382862018999
Order code	62018999
Material Nr. (12NC)	911401509443
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828620189
Numerator - Packs per outer box	4
EAN/UPC - Case	6923828620189

