



# GreenSpace Grid

## GD309B 3\*P20 930 PSU-E MB

GreenSpace Grid, 54 W, 66 W, 930 warm white, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Grid product family offers a complete range of options with comprehensive control availability, optical solutions and powerful lumen outputs, meanwhile ensures the product reliability and quality within compact luminaire body.

### Product data

General Information		Protection class IEC	
Light source engine type	LED	Safety class II	
Value ladder	Performance	Controls and Dimming	
<b>Light Technical</b>		Dimmable	No
Luminous Flux	5,400 lm	Control interface	-
Correlated Color Temperature (Nom)	3000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	90 lm/W	Housing Material	Aluminum Alloy
Color rendering index (CRI)	>90	Optical cover material	Acrylate
Light source color	930 warm white	Housing Color	White
<b>Operating and Electrical</b>		Optical cover finish	Frosted
Input Voltage	200 to 240 V	Ingress protection code	IP20 [Finger-protected]
Line Frequency	50 to 60 Hz	Mech. impact protection code	IK03 [0.3 J]
Power Consumption	54 66 W	Optical cover type	Acrylate
Power Factor (Fraction)	0.9	Net Weight (Piece)	2.030 kg
Number of products on MCB of 16 A type B	-		

# GreenSpace Grid

## Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

## Product Data

Order product name	GD309B 3*P20 930 PSU-E MB
--------------------	---------------------------

Full product name	GD309B 3*P20 930 PSU-E MB
Full product code	872016953089899
Order code	911401511312
Material Nr. (12NC)	911401511312
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169530898
Numerator - Packs per outer box	4
EAN/UPC - Case	8720169542389

## Dimensional drawing

