



Flex Cove - Neon Indoor

LS360S LED2 P6 4000K L5 0612 S

Flex Cove - Neon Indoor, 205 lm, 33 lm/W, 940 neutral white, Opal, 24 V, IP44 | Wire-protected, splash-proof

Philips FlexCove Neon Indoor is a NEW offer in addition to our popular LED cove lighting. This comprehensive new family of flexible strip lights are designed to follow straight lines or curves to create beautiful ambiances that highlight architectural details in mono white, tunable white or colored light. These customizable cove lighting strips also promise superb lighting uniformity within small light mixing distances and limited installation spaces, color consistency and easy installation. All with a long lifetime that promises less lumen decay or color shifts. So with FlexCove Neon Indoor, you can flex your accent lighting to suit the requirements of any project - beautifully.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance

Light Technical	
Luminous Flux	205 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	33 lm/W
Color rendering index (CRI)	90
Light source color	940 neutral white
Unified glare rating CEN	Not applicable

Operating and Electrical	
Input Voltage	24 V
Line Frequency	- Hz
Power Consumption	30.5 W
Power Factor (Fraction)	-
Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class III

Controls and Dimming	
Dimmable	Yes - Check ballast compatibility
Control interface	depends on driver (1-10V, DALI...)

Flex Cove - Neon Indoor

Mechanical and Housing	
Housing Material	Silicon
Optical cover material	Silicon tube
Housing Color	White
Optical cover finish	Opal
Overall length	5,000 mm
Overall width	6 mm
Overall height	12 mm
Dimensions (Height x Width x Depth)	12 x 6 x 5000 mm
Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Without lens
Net Weight (Piece)	0.355 kg

Approval and Application	
Flammability mark	-
CE mark	No

Performance	
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +45 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	LS360S LED2 P6 4000K L5 0612 S
Full product name	LS360S LED2 P6 4000K L5 0612 S
Order code	911401516544
Material Nr. (12NC)	911401516544
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

Dimensional drawing

