

# Greenperform Cleanroom Teardrop G2

## CR388C LED20 Amber L120 PSU

Greenperform Cleanroom Teardrop G2, 21 W, Yellow, 2200 lm, Symmetrical, IP40 | Wire-protected

Greenperform Cleanroom Teardrop G2 is an optimized cleanroom lighting fixture. With its slim, compact and smooth housing design, Teardrop G2 maximally avoids dust attached in cleanroom application, and can meet the classification 10 ~1000. CR388C series products also provide excellent lighting quality, substantial energy saving and reliable quality of maintenance free. Both white and yellow lighting solutions are available, Teardrop G2 is your excellent option for both new projects and retrofit projects.

### Product data

General Information		Luminous Efficacy (rated) (Nom)	
Light source replaceable	No		105 lm/W
Number of gear units	1 unit	Color rendering index (CRI)	-
Driver included	Yes	Light source color	Yellow
Light source engine type	LED	Optic type	Symmetrical
Value ladder	Performance	Luminaire light beam spread	120°
Warranty period	3 years		
Light Technical		Operating and Electrical	
Luminous Flux	2,200 lm	Input Voltage	220 to 240 V
Correlated Color Temperature (Nom)	-	Line Frequency	50 to 60 Hz
		Inrush current	14 A
		Inrush time	0.25 ms

## Greenperform Cleanroom Teardrop G2

Power Consumption	21 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Number of products on MCB of 16 A type B	33
Protection class IEC	Safety class I

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

### Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	White
Optical cover finish	Opal
Overall length	1,200 mm
Overall width	45 mm
Overall height	84 mm
Dimensions (Height x Width x Depth)	84 x 45 x 1200 mm
Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Polycarbonate

Net Weight (Piece)	1.199 kg
--------------------	----------

### Approval and Application

Glow-wire test	Temperature 750 °C, duration 5 s
CE mark	No
EU RoHS compliant	Yes
Ambient temperature range	0 to +35 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%


### Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	45,000 hour(s)
Median useful life L90B50	40,000 hour(s)

### Product Data

Order product name	CR388C LED20 Amber L120 PSU
Full product name	CR388C LED20 Amber L120 PSU
Full product code	911401516941
Order code	911401516941
Material Nr. (12NC)	911401516941
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing



## Greenperform Cleanroom Teardrop G2

