



# Truefashion Projector GCGM

## GD700B LED20 930PW PSU MB WH

Truefashion Projector GCGM, 21.2 W, 1685 lm, 3000 K

Truefashion Projector is offering a retail segment with attractive outlook design, excellent quality of light & dedicated light recipe as well as system connectivity, to create a comfortable ambiance and impressive shopping experience to stimulate the store sales for retail customers.

### Warnings and Safety

- 3 years

### Product data

General Information	
Light source engine type	LED
Service tag	Yes
Value ladder	Specification

  

Light Technical	
Luminous Flux	1,685 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	79 lm/W
Color rendering index (CRI)	>90
Light source color	930 warm white

  

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz

  

Power Consumption	
Power Consumption	21.2 W
Power Factor (Fraction)	0.97
Number of products on MCB of 16 A type B	1
Protection class IEC	Safety class II

  

Controls and Dimming	
Dimmable	No
Control interface	-

  

Mechanical and Housing	
Housing Material	Aluminum
Optical cover material	Polymethyl methacrylate
Housing Color	White RAL 9003
Optical cover finish	-
Overall length	100 mm

# Truefashion Projector GCGM

Overall width	100 mm
Overall height	75 mm
Dimensions (Height x Width x Depth)	75 x 100 x 100 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	-
Optical cover type	Lens
Net Weight (Piece)	0.350 kg

## Approval and Application

CE mark	Yes
Ambient temperature range	-15 to +35 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

## Product Data

Order product name	GD700B LED20 930PW PSU MB WH
Full product name	GD700B LED20 930PW PSU MB WH
Full product code	911401518571
Order code	911401518571
Material Nr. (12NC)	911401518571
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing

