



GreenSpace Flex Luna

RS378B P27 930 PSU-E MB M70 WP PRO

GreenSpace Flex Luna, 27.5 W, 930 warm white, IP20/54 |
 Finger-protected; dust accumulation-protected, splash-proof

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance
Light Technical	
Luminous Flux	3,185 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	116 lm/W
Color rendering index (CRI)	92
Light source color	930 warm white
Unified glare rating CEN	16
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	27.5 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B 33	

Protection class IEC	Safety class II
Controls and Dimming	
Dimmable	-
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Polycarbonate
Housing Color	Black
Optical cover finish	Structured optic
Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]
Mech. impact protection code	IK03 [0.35 J reinforced]
Optical cover type	Lens
Net Weight (Piece)	0.565 kg

GreenSpace Flex Luna

Approval and Application

CE mark	Yes
Ambient temperature range	-20 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Product Data

Order product name	RS378B P27 930 PSU-E MB M70 WP PRO
--------------------	------------------------------------

Full product name	RS378B P27 930 PSU-E MB M70 WP PRO
Order code	911401518746
Material Nr. (12NC)	911401518746
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	18

Dimensional drawing

