



# Flex Cove - Neon Indoor

## LS360S LED4 P11 RGBW L5 1616 T

Flex Cove - Neon Indoor, 360 lm, 32 lm/W, RGBW, Opal, 24 V, IP44 | Wire-protected, splash-proof

Philips FlexCove Neon Indoor is a NEW offer in addition to our popular LED cove lighting. This comprehensive new family of flexible strip lights are designed to follow straight lines or curves to create beautiful ambiances that highlight architectural details in mono white, tunable white or colored light. These customizable cove lighting strips also promise superb lighting uniformity within small light mixing distances and limited installation spaces, color consistency and easy installation. All with a long lifetime that promises less lumen decay or color shifts. So with FlexCove Neon Indoor, you can flex your accent lighting to suit the requirements of any project - beautifully.

### Product data

General Information		Operating and Electrical	
Light source engine type	LED	Input Voltage	24 V
Value ladder	Performance	Line Frequency	- Hz
<b>Light Technical</b>		Power Consumption	46.5 W
Luminous Flux	360 lm	Power Factor (Fraction)	-
Correlated Color Temperature (Nom)	3000 K	Number of products on MCB of 16 A type B	-
Luminous Efficacy (rated) (Nom)	32 lm/W	Protection class IEC	Safety class III
Color rendering index (CRI)	90	<b>Controls and Dimming</b>	
Light source color	RGBW	Dimmable	Yes - Check ballast compatibility
Unified glare rating CEN	Not applicable	Control interface	depends on driver (1-10V, DALI...)

## Flex Cove - Neon Indoor

Mechanical and Housing	
Housing Material	Silicon
Optical cover material	Silicon tube
Housing Color	White
Optical cover finish	Opal
Overall length	5,000 mm
Overall width	16 mm
Overall height	16 mm
Dimensions (Height x Width x Depth)	16 x 16 x 5000 mm
Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Without lens
Net Weight (Piece)	1.380 kg

  

Approval and Application	
Flammability mark	-
CE mark	No

  

Performance	
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +45 °C

  

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

  

Product Data	
Order product name	LS360S LED4 P11 RGBW L5 1616 T
Full product name	LS360S LED4 P11 RGBW L5 1616 T
Order code	911401519044
Material Nr. (12NC)	911401519044
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

## Dimensional drawing

