



# GreenSpace G6

## DN393B LED25/840 P19PSU D200 ALWP GMG2HE

GreenSpace G6, 19.2 W, 2500 lm, 4000 K, Facetted reflector, Matte, IP20/54 | Finger-protected; dust accumulation-protected, splash-proof

Philips GreenSpace G6 builds on the GreenSpace family's reputation for superb performance, extremely low energy use, and high visual comfort. This next generation of reliable LED downlights comes in a highly-compact design with a deep, recessed architecture and increased reflector depth to highlight the smallest of details. GreenSpace G6 is also a shining example of versatility. This energy-saving LED downlight is available in a comprehensive range of configurations from 600 to 3,550 lumen, with the option to choose fixed, dimmable, or Interact Ready variants. This makes GreenSpace G6 the perfect 'mix and match' solution for potentially broad and extended applications that require different lighting ambiances, with one cohesive luminaire look and feel.

### Product data

| General Information      |             | Operating and Electrical           |                    |
|--------------------------|-------------|------------------------------------|--------------------|
| Number of gear units     | -           | Correlated Color Temperature (Nom) | 4000 K             |
| Gear                     | -           | Luminous Efficacy (rated) (Nom)    | 132 lm/W           |
| Driver included          | Yes         | Color rendering index (CRI)        | >80                |
| Light source engine type | LED         | Number of light sources            | 1                  |
| Service tag              | Yes         | Light source color                 | 840 neutral white  |
| Value ladder             | Performance | Optic type                         | Facetted reflector |
| Warranty period          | 3 years     | Unified glare rating CEN           | 17                 |
| Light Technical          |             | Input Voltage                      | 220 to 240 V       |
| Luminous Flux            | 2,500 lm    | Line Frequency                     | 50 or 60 Hz        |

## GreenSpace G6

|  |  |
|--|--|
| Inrush current                           | 10 A   |
| Inrush time                              | 0.02 ms  |
| Power Consumption                        | 19.2 W   |
| Power Factor (Fraction)                  | 0.9  |
| Connection                               | Flying leads/wires                             |
| Cable                                    | 2×0.75mm <sup>2</sup> Cable 0.2 m without plug |
| Number of products on MCB of 16 A type B | 170  |
| Suitable for random switching            | No   |
| Protection class IEC                     | Safety class II                                |

### Controls and Dimming

|                   |                |
|-------------------|----------------|
| Dimmable          | No             |
| Control interface | -              |
| Maximum dim level | Not applicable |

### Mechanical and Housing

|                              |   |
|------------------------------|---|
| Housing Material             | Aluminum die-cast   |
| Reflector material           | Polycarbonate   |
| Optic material               | Polycarbonate   |
| Optical cover material       | Polycarbonate   |
| Housing Color                | Aluminum  |
| Mounting device              | Frame for recessed mounting   |
| Optical cover finish         | Matte   |
| Overall height               | 107 mm  |
| Overall diameter             | 216 mm  |
| Ingress protection code      | IP20/54 [Finger-protected; dust accumulation-protected, splash-proof] |
| Mech. impact protection code | IK03 [0.3 J]  |
| Optical cover type           | Polycarbonate Diffuser  |

|                    |          |
|--------------------|----------|
| Net Weight (Piece) | 0.440 kg |
|--------------------|----------|

### Approval and Application

|                                    |  |
|------------------------------------|--|
| Glow-wire test                     | Temperature 650 °C, duration 5 s               |
| Flammability mark                  | -  |
| CE mark                            | Yes  |
| ENEC mark                          | -  |
| Photobiological risk               | Photobiological risk group 1 @200mm to EN62778 |
| EU RoHS compliant                  | Yes  |
| Performance ambient temperature Tq | 25 °C  |
| Ambient temperature range          | -20 to +40 °C                                  |

### Initial Performance (IEC Compliant)

|                             |        |
|-----------------------------|--------|
| Luminous flux tolerance     | +/-10% |
| Initial chromaticity        | 5      |
| Power consumption tolerance | +/-10% |

### Product Data

|                                 |   |
|---------------------------------|---|
| Order product name              | DN393B LED25/840 P19PSU D200 ALWP<br>GMG2HE |
| Full product name               | DN393B LED25/840 P19PSU D200 ALWP<br>GMG2HE |
| Order code                      | 911401521444                                |
| Material Nr. (12NC)             | 911401521444                                |
| Numerator - Quantity Per Pack   | 1   |
| Numerator - Packs per outer box | 4   |

### Dimensional drawing



