



# GreenSpace Flex Luna

## SM378B R P11 930 PSU-E NB D100 G-TT PRO

GreenSpace Flex Luna, 11.5 W, 1480 lm, 3000 K, Structured optic, IP20 | Finger-protected

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

### Product data

General Information	
Light source engine type	LED
Value ladder	Performance
Light Technical	
Luminous Flux	1,480 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	129 lm/W
Color rendering index (CRI)	92
Light source color	930 warm white
Unified glare rating CEN	16
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	11.5 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	66

Protection class IEC	Safety class II
Controls and Dimming	
Dimmable	-
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Polycarbonate
Housing Color	Black
Optical cover finish	Structured optic
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.35 J reinforced]
Optical cover type	Lens
Net Weight (Piece)	0.416 kg
Approval and Application	
CE mark	Yes

## GreenSpace Flex Luna

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

### Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

### Product Data

Order product name	SM378B R P11 930 PSU-E NB D100 G-TT PRO
--------------------	--

Full product name	SM378B R P11 930 PSU-E NB D100 G-TT PRO
Order code	911401522646
Material Nr. (12NC)	911401522646
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	36

## Dimensional drawing

