



GreenSpace G6

DN393B LED26/865 P19PSU D200 WH GMG2HE

GreenSpace G6, 19.2 W, 2600 lm, 6500 K, White reflector and opal cover, Matte, IP20 | Finger-protected

Philips GreenSpace G6 builds on the GreenSpace family’s reputation for superb performance, extremely low energy use, and high visual comfort. This next generation of reliable LED downlights comes in a highly-compact design with a deep, recessed architecture and increased reflector depth to highlight the smallest of details. GreenSpace G6 is also a shining example of versatility. This energy-saving LED downlight is available in a comprehensive range of configurations from 600 to 3,550 lumen, with the option to choose fixed, dimmable, or Interact Ready variants. This makes GreenSpace G6 the perfect ‘mix and match’ solution for potentially broad and extended applications that require different lighting ambiances, with one cohesive luminaire look and feel.

Product data

General Information		Operating and Electrical	
Number of gear units	-	Color rendering index (CRI)	>80
Gear	-	Number of light sources	1
Driver included	Yes	Light source color	865 cool daylight
Light source engine type	LED	Optic type	White reflector and opal cover
Service tag	Yes	Unified glare rating CEN	25
Value ladder	Performance		
Warranty period	3 years	Input Voltage	220 to 240 V
		Line Frequency	50 or 60 Hz
		Inrush current	10 A
		Inrush time	0.02 ms
		Power Consumption	19.2 W
		Power Factor (Fraction)	0.9
Light Technical			
Luminous Flux	2,600 lm		
Correlated Color Temperature (Nom)	6500 K		
Luminous Efficacy (rated) (Nom)	140 lm/W		

Connection	Flying leads/wires
Cable	2×0.75mm² Cable 0.2 m without plug
Number of products on MCB of 16 A type B 170	
Suitable for random switching	No
Protection class IEC	Safety class II

Controls and Dimming

Dimmable	No
Control interface	-
Maximum dim level	Not applicable

Mechanical and Housing

Housing Material	Aluminum die-cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Aluminum
Mounting device	Frame for recessed mounting
Optical cover finish	Matte
Overall height	107 mm
Overall diameter	216 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Polycarbonate Diffuser
Net Weight (Piece)	0.440 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 5 s
----------------	----------------------------------

Flammability mark	-
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	5
Power consumption tolerance	+/-10%

Product Data

Order product name	DN393B LED26/865 P19PSU D200 WH GMG2HE
Full product name	DN393B LED26/865 P19PSU D200 WH GMG2HE
Full product code	872110334571499
Order code	911401527644
Material Nr. (12NC)	911401527644
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103345714
Numerator - Packs per outer box	4
EAN/UPC - Case	8721103345714

Dimensional drawing



