



Greenspace Flex

RS378B P6 930 PSU-E MB M43

Greenspace Flex, 6 W, 930 warm white, IP20 | Finger-protected

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data

General Information		Control interface	
Light source engine type	LED		-
Value ladder	Performance		
Light Technical		Mechanical and Housing	
Luminous Flux	4,074 lm	Housing Material	Aluminum Alloy
Correlated Color Temperature (Nom)	3000 K	Optical cover material	Polymethyl methacrylate
Luminous Efficacy (rated) (Nom)	97 lm/W	Housing Color	Grey
Color rendering index (CRI)	>90	Optical cover finish	Opal
Light source color	930 warm white	Ingress protection code	IP20 [Finger-protected]
		Mech. impact protection code	IK04 [0.5 J standard plus]
		Optical cover type	PMMA
		Net Weight (Piece)	0.140 kg
Operating and Electrical		Approval and Application	
Input Voltage	220-240 V	CE mark	Yes
Line Frequency	50 or 60 Hz	Ambient temperature range	-20 to +45 °C
Power Consumption	6 W		
Power Factor (Fraction)	0.9	Initial Performance (IEC Compliant)	
Number of products on MCB of 16 A type B	-	Luminous flux tolerance	-10% / +10%
Protection class IEC	Safety class II	Power consumption tolerance	+/-10%
Controls and Dimming			
Dimmable	No		

Greenspace Flex

Product Data	
Order product name	RS378B P6 930 PSU-E MB M43
Full product name	RS378B P6 930 PSU-E MB M43
Full product code	911401532671
Order code	911401532671

Material Nr. (12NC)	911401532671
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	48

Dimensional drawing

