



Greenspace Flex

RS378B P6 927 PSD-E MB M55

Greenspace Flex, 6 W, 927 warm white, DALI, IP20 | Finger-protected

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance

Light Technical	
Luminous Flux	600 lm
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color rendering index (CRI)	>90
Light source color	927 warm white

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	6 W
Power Factor (Fraction)	0.83
Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	DALI
Control interface	DALI

Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Polymethyl methacrylate
Housing Color	Grey
Optical cover finish	Opal
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Optical cover type	PMMA
Net Weight (Piece)	0.250 kg

Approval and Application	
CE mark	Yes
Ambient temperature range	-20 to +45 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

Greenspace Flex

Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data

Order product name	RS378B P6 927 PSD-E MB M55
Full product name	RS378B P6 927 PSD-E MB M55
Full product code	911401535071

Order code	911401535071
------------	--------------

Material Nr. (12NC)	911401535071
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	36
---------------------------------	----

Dimensional drawing

