



Greenspace Flex

RS378B P11 930 PSD-E WB M55

Greenspace Flex, 11 W, 930 warm white, DALI, IP20 | Finger-protected

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data

General Information		Controls and Dimming	
Light source engine type	LED	Dimmable	DALI
Value ladder	Performance	Control interface	DALI
Light Technical		Mechanical and Housing	
Luminous Flux	957 lm	Housing Material	Aluminum Alloy
Correlated Color Temperature (Nom)	3000 K	Optical cover material	Polymethyl methacrylate
Luminous Efficacy (rated) (Nom)	87 lm/W	Housing Color	Grey
Color rendering index (CRI)	>90	Optical cover finish	Opal
Light source color	930 warm white	Ingress protection code	IP20 [Finger-protected]
		Mech. impact protection code	IK04 [0.5 J standard plus]
Operating and Electrical		Optical cover type	PMMA
Input Voltage	220-240 V	Net Weight (Piece)	0.250 kg
Line Frequency	50 or 60 Hz		
Power Consumption	11 W	Approval and Application	
Power Factor (Fraction)	0.83	CE mark	Yes
Number of products on MCB of 16 A type B	-	Ambient temperature range	-20 to +45 °C
Protection class IEC	Safety class II		
		Initial Performance (IEC Compliant)	
		Luminous flux tolerance	-10% / +10%

Greenspace Flex

Power consumption tolerance	+/-10%
Product Data	
Order product name	RS378B P11 930 PSD-E WB M55
Full product name	RS378B P11 930 PSD-E WB M55
Full product code	692382865100899
Order code	911401536371

Material Nr. (12NC)	911401536371
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828651008
Numerator - Packs per outer box	36
EAN/UPC - Case	6923828653415

Dimensional drawing

