



GreenUp hospitality spot

RS318B P9 930 PSU-E WB S

GreenUp hospitality spot, 9 W, 930 warm white, IP20 | Finger-protected

GreenUp hospitality spot is a small cut out spot but with comprehensive offers. It offers flexible wattages for different indoor applications, such as retail and hospitality. This family delivers high CRI90 and 3 different beam angles to perfectly fit the light requirement of indoor retail and hospitality applications.

Product data

General Information	
Light source engine type	LED
Value ladder	Value

Light Technical	
Luminous Flux	75 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	101 lm/W
Color rendering index (CRI)	>90
Light source color	930 warm white

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	0/50/60 Hz
Inrush current	0.045 A
Power Consumption	9 W
Power Factor (Fraction)	0.9

Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Aluminum die-cast
Optical cover material	Polymethyl methacrylate
Housing Color	Aluminum and gray
Optical cover finish	Clear
Overall length	93 mm
Overall width	85 mm
Overall height	93 mm
Overall diameter	85 mm
Dimensions (Height x Width x Depth)	93 x 85 x 93 mm

GreenUp hospitality spot

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.35 J reinforced]
Optical cover type	-
Net Weight (Piece)	0.015 kg

Approval and Application

Flammability mark	-
CE mark	No
Ambient temperature range	+20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	-
Power consumption tolerance	+/-10%

Product Data

Order product name	RS318B P9 930 PSU-E WB S
Full product name	RS318B P9 930 PSU-E WB S
Full product code	872016953298499
Order code	911401538602
Material Nr. (12NC)	911401538602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169532984
Numerator - Packs per outer box	16
EAN/UPC - Case	8720169544475

Dimensional drawing

