



# Greenspace Flex

## RS378B P33 940 PSD-E NB M87

Greenspace Flex, 33 W, 940 neutral white, DALI, IP20 | Finger-protected

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

### Product data

General Information	
Light source engine type	LED
Value ladder	Performance

  

Light Technical	
Luminous Flux	2,400 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	73 lm/W
Color rendering index (CRI)	>90
Light source color	940 neutral white

  

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	33 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	DALI
Control interface	DALI

  

Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Polymethyl methacrylate
Housing Color	Grey
Optical cover finish	Opal
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Optical cover type	PMMA
Net Weight (Piece)	0.850 kg

  

Approval and Application	
CE mark	Yes
Ambient temperature range	-20 to +45 °C

  

Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

## Greenspace Flex

Power consumption tolerance	+/-10%
-----------------------------	--------

### Product Data

Order product name	RS378B P33 940 PSD-E NB M87
Full product name	RS378B P33 940 PSD-E NB M87
Full product code	911401539171

Order code	911401539171
------------	--------------

Material Nr. (12NC)	911401539171
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	12
---------------------------------	----

## Dimensional drawing

