



# GreenSpace Flex Luna

## SM378B S P12 PSD-TNW WB D100 G-TT PRO

GreenSpace Flex Luna, 13 W, 1070 lm, Tunable White, DALI, Structured optic, IP20 | Finger-protected

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

### Product data

General Information		Protection class IEC	
Light source engine type	LED	Safety class II	
Value ladder	Performance	Controls and Dimming	
<b>Light Technical</b>		Dimmable	DALI
Luminous Flux	1,070 lm	Control interface	DALI
Correlated Color Temperature (Nom)	Tunable White	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	82 lm/W	Housing Material	Aluminum Alloy
Color rendering index (CRI)	90	Optical cover material	Polycarbonate
Light source color	Tunable white	Housing Color	Black
Unified glare rating CEN	16	Optical cover finish	Structured optic
<b>Operating and Electrical</b>		Ingress protection code	IP20 [Finger-protected]
Input Voltage	220 to 240 V	Mech. impact protection code	IK03 [0.35 J reinforced]
Line Frequency	50 or 60 Hz	Optical cover type	Lens
Power Consumption	13 W	Net Weight (Piece)	0.615 kg
Power Factor (Fraction)	0.9	Approval and Application	
Number of products on MCB of 16 A type B	70	CE mark	No

# GreenSpace Flex Luna

Ambient temperature range	-20 to +45 °C
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	SM378B S P12 PSD-TNW WB D100 G-TT PRO

Full product name	SM378B S P12 PSD-TNW WB D100 G-TT PRO
Order code	911401539446
Material Nr. (12NC)	911401539446
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24

## Dimensional drawing

