



# GreenPerform Highbay G5

## BY698P G5 LED200/NW PSU WB GM L3m

GreenPerform Highbay G5, 121 W, 20500 lm, 4000 K, 85°

The GreenPerform Highbay G5 continues the GreenPerform family’s enviable reputation for reliable performance. Not only does it deliver leading system efficacy and extended long-term quality, it also promises Unified Glare Rating (UGR) control with compact dimensions. GreenPerform Highbay G5 is also fully compatible with IoT software such as Interact, which is a scalable, future-proof control system. The family also has a series that supports cold room applications with 100% humidity and no condensation. All benefits than make this robust, optimized, and versatile family suitable for almost all industrial applications.

### Product data


| General Information                |             |                             |                   |
|------------------------------------|-------------|-----------------------------|-------------------|
| Number of gear units               | 1 unit      | Beam angle of light source  | 115 degree(s)     |
| Gear                               | -           | Light source color          | 840 neutral white |
| Driver included                    | Yes         | Optic type                  | Wide beam         |
| Light source engine type           | LED         | Luminaire light beam spread | 85°               |
| Value ladder                       | Performance | Unified glare rating CEN    | 25                |
| Warranty period                    | 5 years     | Effective projected area    | 0 m²              |
| Light Technical                    |             | Operating and Electrical    |                   |
| Luminous Flux                      | 20,500 lm   | Input Voltage               | 220 to 240 V      |
| Correlated Color Temperature (Nom) | 4000 K      | Line Frequency              | 50 or 60 Hz       |
| Luminous Efficacy (rated) (Nom)    | 169 lm/W    | Inrush current              | 41.6 A            |
| Color rendering index (CRI)        | 80          | Inrush time                 | 0.665 ms          |
| Number of light sources            | 1           | Power Consumption           | 121 W             |
|                                    |             | Power Factor (Fraction)     | 0.95              |

GreenPerform Highbay G5

|                                            |                                              |
|--------------------------------------------|----------------------------------------------|
| Connection                                 | Flying leads/wires                           |
| Cable                                      | Cable 3.0 m without plug                     |
| Number of products on MCB of 16 A type B 6 |                                              |
| Suitable for random switching              | Yes                                          |
| Protection class IEC                       | Safety class I                               |
| Controls and Dimming                       |                                              |
| Dimmable                                   | -                                            |
| Control interface                          | -                                            |
| Maximum dim level                          | Not applicable                               |
| Mechanical and Housing                     |                                              |
| Housing Material                           | Aluminum die-cast                            |
| Reflector material                         | -                                            |
| Optic material                             | Polycarbonate                                |
| Optical cover material                     | Polycarbonate                                |
| Housing Color                              | Grey                                         |
| Mounting device                            | Suspension set simple, standard              |
| Optical cover finish                       | Clear                                        |
| Overall height                             | 99 mm                                        |
| Overall diameter                           | 330 mm                                       |
| Ingress protection code                    | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code               | IK08 [5 J vandal-protected]                  |
| Optical cover type                         | Clear dome                                   |
| Net Weight (Piece)                         | 2.940 kg                                     |
| Approval and Application                   |                                              |
| Glow-wire test                             | Temperature 650 °C, duration 30 s            |
| Flammability mark                          | For mounting on normally flammable surfaces  |

|                                     |                                                |
|-------------------------------------|------------------------------------------------|
| CE mark                             | Yes                                            |
| ENEC mark                           | -                                              |
| Photobiological risk                | Photobiological risk group 1 @200mm to EN62778 |
| Photobiological risk specification  | 0.2 m                                          |
| EU RoHS compliant                   | Yes                                            |
| Performance ambient temperature Tq  | 35 °C                                          |
| Ambient temperature range           | -30 °C to 50 °C                                |
| UV                                  |                                                |
| UV-C radiation                      | 0 W                                            |
| UV-C irradiance defined at 0.2m     | 0 mW/m²                                        |
| Initial Performance (IEC Compliant) |                                                |
| Luminous flux tolerance             | -10% / +10%                                    |
| Initial chromaticity                | (0.386, 0.384) SDCM<5                          |
| Power consumption tolerance         | +/-10%                                         |
| Product Data                        |                                                |
| Order product name                  | BY698P G5 LED200/NW PSU WB GM L3m              |
| Full product name                   | BY698P G5 LED200/NW PSU WB GM L3m              |
| Full product code                   | 872110330791000                                |
| Order code                          | 911401539545                                   |
| Material Nr. (12NC)                 | 911401539545                                   |
| Numerator - Quantity Per Pack       | 1                                              |
| EAN/UPC - Product/Case              | 8721103307910                                  |
| Numerator - Packs per outer box     | 1                                              |
| EAN/UPC - Case                      | 8721103307910                                  |

Dimensional drawing



## GreenPerform Highbay G5

